



VOC sensor Datasheet

SGX Solid Polymer Electrolyte Gas Sensors

The SGX series of PS1 and PS4 Electrochemical gas sensors are using a revolutionary 'Solid Polymer Electrolyte' technology that is based on the principle of catalytic reaction. The target gas to be measured generates a very small current, proportional to the gas concentration. Our technology offers a stable, high quality and cost-effective manufacturing process. The SGX solid polymer electrolyte gas sensors are available in a very small size, are highly sensitive, do not use power and have very low cross sensitivity from other gases.





SGX Europe Sp. z o.o. Building 11 Ligocka St. 103, 40-568 Katowice, Poland

T: +48 (0) 32 438 4778

E: sales.is@sgxsensortech.com www.sgxsensortech.com

Technical Specifications

Performance

Sensitivity		55 ± 15 nA / ppm	
Measurement Range		0 – 200ppm	
Zero Current	\supset	± 100 nA	
Maximum Overload		1000 ppm	
Response Time	$\overline{)}$	T50 < 10s, T90 < 30s	
Repeatability		1%	
Lower Detectable Limit (LDL)	\supset	< 1 ppm	
Linear Range		200 ppm	
Resolution (16Bit ADC)		0.1ppm	



Temperature Range	-40°C to +55°C		
Pressure Range	800 to 1200 hPA		
Operating Humidity Range	15-95% RH		
Storage Temperature	0 to 20℃		

Lifetime Details

Long-Term Drift	< 1 %/month
Expected Lifetime	> 3 years in air
Zero Drift in Clean Air	< 2 ppm
Storage conditions	0-20 °C
Storage Life	12 months
Warranty	12 months

Operation

Operating Principle	Amperometric, 3-electrode
Bias Voltage	0 mV
Recommended Load Resistor	100 Ω
Warm Up Time	< 60 s

Housing

Housing Material	PPO		
Weight	PS1-VOC-200 < 0.7g PS4-VOC-200 < 6g		



PS1-VOC-200



PS4-VOC-200

Features

- Small size
- · High sensitivity
- Wide temperature range
- Fast response time
- · No electrolyte leakage
- · Low cost at large volumes
- Individually calibrated (including test report)

Key applications

- General Gas Detection
- Consumer Market
- VOC Gas Detection
- · Mobile Phone Nose
- Indoor & Outdoor Air Quality
- Low Power Nose

Important Notes

- All performance is based on conditions at 20°C, 50% RH and 1 atm, flow rate>150qcm/min, using SGX recommended circuitry.
- Sensor performance is temperature dependant; please contact SGX for temperature performance other than 20°C.
- Do not solder to the connector pins as this may damage the sensor and thereby invalidate the warranty.
- Details on recommended connector pins can be found in the Frequently Asked Questions within the Gas Sensor section of the SGX website.









An Amphenol Company

SGX Europe Sp. z o.o. Building 11 Ligocka St. 103, 40-568 Katowice, Poland

T: +48 (0) 32 438 4778

E: sales.is@sgxsensortech.com www.sgxsensortech.com

Cross Sensitivity

Gas	Formula	Test Concentration	Sensor Reading
Acetaldehyde	C ₂ H ₄ O	5ppm	3.84ppm
Acetic Acid	CH₃COOH	5ppm	1.1ppm
Acetylene	C ₂ H ₂	5ppm	1.64ppm
Acrylonitrile	C ₃ H ₃ N	5ppm	0.4ppm
Ammonia	NH ₃	5ppm	1.5ppm
Benzene	C ₆ H ₆	5ppm	1.1ppm
Butadiene	C ₄ H ₆	5ppm	8.68ppm
Carbon Disulfide	CS ₂	5ppm	1.23ppm
Carbon Monoxide	CO	5ppm	3.38ppm
Dimethyl Disulfide	C ₂ H ₆ S ₂	2ppm	6.79ppm
Dining Lampblack (Dimensionless)	Unsaturated hydrocarbons	1	4.65ppm
Ethanol	C ₂ H ₆ O	5ppm	1.83ppm
Ethyl Mercaptan	C₂H ₆ S	5ppm	8.97ppm
Ethylene	C ₂ H ₄	5ppm	0.59ppm
Formaldehyde	НСНО	5ppm	5.29ppm
Formic Acid	нсоон	5ppm	5.37ppm
Gasoline Volatilization (Dimensionless)	Aliphatic hydrocarbons, cycloalkanes, aromatic hydrocarbons	I	5.5ppm
Hydrogen	H ₂	5ppm	1.15ppm
Hydrogen Chloride	HCL	5ppm	0.27ppm
Hydrogen Cyanide	HCN	5ppm	0.36ppm
Isobutene	C ₄ H ₈	5ppm	5ppm
Methanol	CH ₄ O	5ppm	5.96ppm
Methyl Mercaptan	CH₄S	5ppm	7ppm
P-xylene	C ₈ H ₁₀	5ppm	0.59ppm
Styrene	C ₈ H ₈	0.5ppm	7.5ppm
Sulphur Dioxide	C₃H ₈ O	5ppm	5ppm
Toluene	C ₇ H ₈	5ppm	0.81ppm
Trimethylamine	C ₃ H ₉ N	5ppm	0.65ppm
	· ·		-

Note:

- 1) The above interference factors may vary due to different sensors and service life, please refer to the actual test results. 2) This table is not complete for all cross gases, other gas please contact with us.





SGX Europe Sp. z o.o. Building 11 Ligocka St. 103, 40-568 Katowice, Poland


T: +48 (0) 32 438 4778

E: sales.is@sgxsensortech.com www.sgxsensortech.com


Dimensions









PS1-VOC-200








PS4-VOC-200

Temperature Curve



DISCLAIMER:

SGX Europe Sp. z o.o. reserves the right to change design features and specifications without prior notification. We do not accept any legal responsibility for customer applications of our sensors. SGX Europe Sp. z o.o. accepts no liability for any consequential losses, injury or damage resulting from the use of this document, the information contained within or from any omissions or errors herein. This document does not constitute an offer for sale and the data contained is for guidance only and may not be taken as warranty. Any use of the given data must be assessed and determined by the user thereof to be in accordance with federal, state and local laws and regulations. All specifications outlined are subject to change without notice.

SGX Europe Sp. z o.o. sensors are designed to operate in a wide range of harsh environments and conditions. However, it is important that exposure to high concentrations of solvent vapours is to be avoided, both during storage, fitting into instruments and operation. When using sensors on printed circuit boards (PCBs), degreasing agents should be used prior to the sensor being fitted. SGX Europe Sp. z o.o. makes every effort to ensure the reliability of its products. Where life safety is a performance requirement of the product, we recommend that all sensors and instruments using these sensors are checked for response to gas before use.

Copyright© 2012-2022 SGX Sensortech All rights reserved.

Trademarks and registered trademarks are the property of their respective owners.

No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, including photocopying, recording, or other electronic or mechanical methods, without the prior written permission of the publisher, except in the case of brief quotations embodied in critical reviews and certain other non-commercial uses permitted by copyright law.

For permission requests or technical support please contact or write to the publisher, addressed "Attention: Permissions Coordinator,".