
Technical Data Sheet

TNC ATTENUATOR 13 DB 3 GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

Technical Data Sheet

TNC ATTENUATOR 13 DB 3 GHZ 1W



	ISSUE 30	-03-20B	SERIES ATTENUAT	OR	PART	NUMBER	R412513124
			ELE	ECTRICAL CHA	ARACTERISTICS		
Fre	quency (GHz)		DC - 2	2 - 3			
	S.W.R (≤)		1.20	1.30	-		
	viation(±dB)		0.5	0.5	-		
			I				
Op	erating Freque	ncy Range	e		DC - 3		GHz
Imp	Impedance			50			Ω
Nominal Attenuation					13		dB
Peak power at 25°C (1µs, 1%)			%0)	100			W
Average power at 25°C				1			W (Free Air Cooled)
							W (Conduction Cooled)
	nnectors ight	T	NC 16,77 g	Male F	emale		MIL-C 39012
vve	igni		10,77	1			
			bow er (%) 100 0 00 00 00 00 00 00 00 00 00 00 00 0	40 -7,5	Versus temperature	85	
			Power (%)	40 -7,5		85	
			Power (%)	40 -7,5	25 55 operature (°C)	85	
			Power (%)	40 -7,5	25 55 operature (°C)	85	
			90 70 (%) Jawod 20 10 0	40 -7,5 Terr	25 55 operature (°C)	85	
			90 70 (%) Jawod 20 10 0	40 -7,5	25 55 operature (°C)	85	
			90 70 (%) Jawod 20 10 0	40 -7,5 Terr	25 55 operature (°C)	85	
			90 70 (%) Jawod 20 10 0	40 -7,5 Terr	25 55 operature (°C)	85	

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.