



TNC ATTENUATOR 17 DB 3 GHZ 1W




PAGE 1/2 ISSUE 08-04-20B SERIES PART NUMBER R412517124 ATTENUATOR





SCALE 1:1



All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact Female center contact Outer contact	BRASS BRASS BERYLLIUM COPPER	NICKEL 2 GOLD 1 OVER NICKEL 2 GOLD 1 OVER NICKEL 2
Insulator Gasket Substrate Resistor Others parts	PTFE SILICONE RUBBER ALUMINA THICK FILM	





TNC ATTENUATOR 17 DB 3 GHZ 1W

PAGE 2/2	ISSUE 08-04-20B	SERIES ATTENUATOR	PART NUMBER R412517124
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2	2 - 3
V.S.W.R (≤)	1.20	1.30
Deviation(±dB)	0.70	0.70

Operating Frequency Range	DC - 3	GHz
Impedance	50	Ω
Nominal Attenuation	17	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	1	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	TNC	Male Female	MIL-C 39012
Weight	16,77	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-40 / +85	°C
Storage temperature range	-40 / +85	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS