



# SS32 THRU SS3200


## Surface Mount Schottky Rectifiers

### Features

- Low profile package
- Ideal for automated placement
- Fast switching for high efficiency
- High forward surge capability
- High temperature soldering:  
260°C/10 seconds at terminals
- Component in accordance to  
RoHS 2002/95/1 and WEEE 2002/96/EC




SMB(DO-214AA)



### Mechanical Data

- **Case:** JEDEC DO-214AA molded plastic body
- **Terminals:** Solder plated, solderable per J-STD-002B and JESD22-B102D
- **Polarity:** Laser band denotes cathode end



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics Rating at 25°C

ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	SYMBOL	SS 32	SS 34	SS 345	SS 36	SS 38	SS 310	SS 3150	SS 3200	Unit
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	20	40	45	60	80	100	150	200	V
Maximum RMS Voltage	V <sub>RMS</sub>	14	28	31	42	56	70	105	140	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	20	40	45	60	80	100	150	200	V
Average Rectified Output Current @T <sub>L</sub> =100°C								3.0		A
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I <sub>FSM</sub>							80		A
Forward Voltage @IF=3.0A (Note 1)	V <sub>FM</sub>		0.55		0.7		0.85		0.92	V
Peak Reverse Current @T <sub>A</sub> =25°C	I <sub>R</sub>			0.1			0.05			mA
At Rated DC Blocking Voltage @T <sub>A</sub> =100°C				10			5			
I <sup>2</sup> t Rating for fusing (t <8.3ms)	I <sup>2</sup> t				26.56					A <sup>2</sup> s
Typical Junction Capacitance (Note 2)	C <sub>J</sub>					12				pF
Typical Thermal Resistance per leg (Note3)	R <sub>θ JA</sub>					70				°C/W
Operating Temperature Range	T <sub>J</sub>				-55 to +150					°C
Storage Temperature Range	T <sub>STG</sub>				-55 to +150					°C

Note: 1.Pulse Test with PW=300usec,1%Duty Cycle.

2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C.

3.Thermal Resistance from Junction to lead mounted on P.C.B. with 0.3" x 0.3" (8.0 mm x 8.0 mm) copper pad areas.



# SS32 THRU SS3200

## Surface Mount Schottky Rectifiers

### Characteristic Curves ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Fig. 1 Forward Current Derating Curve




Fig. 2 Typ. Forward Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




FIG.4 TYPICAL REVERSE CHARACTERISTIC




FIG.5 MOUNTING PAD LAYOUT

