
## **Technical Data Sheet**

7-16 ATTENUATOR 6 DB 3 GHZ 100W





**BLACK PAINTING** 

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

SILICONE RUBBER

ALUMINA

THICK FILM

ALUMINIUM

Gasket

Substrate Resistor


Others parts

## **Technical Data Sheet**

7-16 ATTENUATOR 6 DB 3 GHZ 100W



E <b>2/2</b>	ISSUE 10-10	ISSUE 10-10-18B SERIE ATTENU		PAR	T NUMBER	R420706110
			ELECTRICAL CH	IARACTERISTICS		
Free	quency (GHz)	DC - 1	1 - 2	2 - 3		
	.W.R (≤)	1.10	1.25	1.30		
	riation(±dB)	1	1	1.5		
	. ,					
Ope	Operating Frequency Range Impedance			DC - 3		GHz
			50			Ω
Nom	Nominal Attenuation			6		dB
Pea	Peak power at 25°C (1µs, 1%) Average power at 25°C		5000			W
Ave	rage power at 25	Э́с		100		W (Free Air Cooled)
Ave	rage power at 25	°C		100		W (Free Air Cooled) W (Conduction Cooled)
				ARACTERISTICS		W (Conduction Cooled)
Con	nectors	7-16	Male			, ,
	nectors	7-16 870,23(	Male	IARACTERISTICS Female		W (Conduction Cooled)
Con	nectors	7-16 870,230	Male D0 g	ARACTERISTICS Female CHARACTERISTIC		W (Conduction Cooled)
Con	nectors	7-16 870,230	Male	IARACTERISTICS Female CHARACTERISTIC	<u>.</u>	W (Conduction Cooled)



## SPECIFICATION

## **OTHER CHARACTERISTICS**