

GBJ10005 -GBJ1010/G

Mechanical Data

Single Phase 10Amp Glass passivated Bridge Rectifiers

Features

- · Glass passivated die construction
- · Low forward voltage drop
- · High current capability
- · High surge current capability
- Plastic material-UL flammability 94V-0
- The G suffix is uses for photoresist chip, otherwise it is a knife scraping chip

MECHANICAL DATA

· Case: Molded plastic, GBJ

• Terminals: Plated Leads Solderable perMIL-STD-202, Method 208

· Polarity: As Marked on Case

Mounting Position: AnyMarking: Type Number

• Lead Free: For RoHS / Lead Free Version

1.Output Anode(+) 2.Input pin(~) 3.Input pin(~) 4.Output Cathode(-)

Maximum Ratings And Electrical Characteristics (@T_A=25°C unless otherwise noted)

0	Parameter	GBJ	GBJ	GBJ	GBJ	GBJ	GBJ	GBJ		
Symbol		10005	1001	1002	1004	1006	1008	1010	Unit	
V_{RRM}	repetitive peak reverse voltage	50	100	200	400	600	800	1000		
V_{RWM}	Working Peak Reverse Voltage	50	100	200	400	600	800	1000	V	
V _{RMS}	RMS voltage	35 70 140 280 420 560 7		700	7 V					
V _{DC}	DC blocking voltage	50	100	200	400	600	800	1000		
IF _{AV}	Average Rectified Output	10.0						А		
	Current (Note 1)@T _C =90°C									
I _{FSM}	Peak forward surge current, 8.3ms single	200						А		
	half sine-wave									
I _t ²	I _t ² Rating for fusing (t<8.3ms)	166				A _S ²				
\/	Forward Voltage @IF=5A	1.0 1.10						V		
V _{FM}	per element @IF=10A									
I _R	Peak Reverse Current@T _A =25°C	5.0					uA			
	at rated DC blocking voltage @T _A =125°C	500								
CJ	Typical junction capacitance	55			pF					
$R_{\theta JA}$	Between junction and ambient, Without heatsink	14			°C/W					
R _{0JC}	Between junction and case, With heatsink	1.4								
TJ	Operation Temperature Range	-55 to +150				°C				
T _{STG}	Storage Temperature Range	-55 to +150								

Note:(1)Thermal resistance from junction to case per element. Unit mounted on 75x75x1.6mm aluminum plate heat sink. **BORN SEMICONDUCTOR**, **INC. ALL**

Revision: 2022-Jan-1





GBJ10005 -GBJ1010/G

Revision: 2022-Jan-1

Single Phase 10Amp Glass passivated Bridge Rectifiers

Ratings And Characteristic Curves

Figure 1: Output Current Derating Curve




Figure 2: Typical Forward Characteristics (per leg)




Figure 3:Maximum Peak Forward Surge Current (per




Figure 4:Typical Junction Capacitance





Figure 5:TYPICAL REVERSE CHARACTERISTICS



BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED







GBJ10005 -GBJ1010/G

Single Phase 10Amp Glass passivated Bridge Rectifiers

Outline Drawing -GBJ





Revision: 2022-Jan-1

SYMBOL	MILLIMETER							
STWIDOL	MIN.	MAX.						
Α	29.70	30.3						
В	19.70	20.3						
С	17.00	18.00						
D	3.80	4.20						
Е	7.30	7.70						
G	9.80	10.20						
Н	2.00	2.40						
I	0.90	1.10						
J	2.30	2.70						
K	3.0x45°							
L	4.40	4.80						
М	3.40	3.80						
N	3.10	3.40						
Р	2.50	2.90						
R	0.60	0.80						
S	10.80	11.20						