
PAF	RQA-5402							
REV	DESCRIPTION	DWN	DATE	APPROVED				
_	ENGINEERING RELEASE	JDM	3/27/15	JDMc				



SPECIFICATIONS:

IMPEDANCE: 50 Ohms FREQUENCY RANGE: 0-6 GHz

VSWR: 1.3 MAX. @ 3GHz

DIELECTRIC WITHSTANDING VOLTAGE: 1000 V rms MIN.

DURABILITY: 100 CYCLES MIN.

TEMPERATURE RANGE: -65°C TO 165°C

3	CONTACT	1	BeCu	Silver
2	INSULATOR	2	PTFE	
1	BODY	1	BRASS	White-Bronze
#	DESCRIPTION	QTY	MATERIAL	FINISH

CUSTOMER OUTLINE DRWING

ALL DIMENSIONS ARE REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES AND [MILLIMETERS]

DRAWN JDMc	3/25/15	
CHECKED		1
		1
orj drawn JDMc	3/25/15	

PROPRIETARY AND CONFIDENTIAL

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY
UNAUTHORIZED USE OF THIS
DRAWING IS EXPRESSLY
PROHIBITED WITHOUT WRITTEN
PERMISSION FROM RF INDUSTRIES. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.



7610 MIRAMAR RD. SAN DIEGO, CA 92126

QMA MALE TO FEMALE RIGHT ANGLE, ADAPTER

	SIZE	CABLE	GROUP	DWG	NO.					REV	
N.	$ \wedge $	l Ni	/Λ		D/	-AC	54	n 2		_	_
IS		1 /	/ ^		111	# n -	VT	UZ			
	SCALE: ENG		ENGINEE	RING ID	<u>; </u>	^		CLIEFT	4	٥٢	1
		NTS			U	U		SHEET	ı	OF	1