

SURFACE MOUNT MICROPROCESSOR CRYSTAL


Page 1 of 3

RT3215-32.768-7-EXT-TR-NS1


SPECIFICATIONS

PARAMETER	VALUE
FREQUENCY RANGE	32.768 kHz
FREQUENCY TOLERANCE AT 25°C	±20 ppm max
TURNOVER TEMPERATURE	+25 ±5°C
TEMPERATURE COEFFICIENT	-0.04 x 10 ⁻⁶ /Δ °C ² max
SHUNT CAPACITANCE	0.9 to 1.2pF
LOAD CAPACITANCE	7 pF
EQUIVALENT SERIES RESISTANCE	65K Ω
DRIVE LEVEL	0.5 μW max
AGING	±3 ppm first year max
OPERATING TEMPERATURE RANGE	-40°C to +85°C
STORAGE TEMPERATURE RANGE	-55°C to +125°C
INSULATION RESISTANCE	500 MΩ max

MECHANICAL SPECIFICATION



CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

PACKAGING


330 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481



REFLOW PROFILE

RT3215-32.768-7-EXT-TR-NS1



Reflow profile		
Temperature Min Preheat	T _{SMIN}	150°C
Temperature Max Preheat	T _{SMAX}	200°C
Time (T _{SMIN} to T _{SMAX})	t _S	60-180 sec.
Temperature	T∟	217°C
Peak Temperature	T _P	260°C
Ramp-up rate	R _{UP}	3°C/sec max.
Ramp-down rate	R _{DOWN}	6°C/sec max.
Time within 5°C of Peak Temperature	t _P	10 sec.
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.
Time	t _L	60-150 sec.

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	COMPLIANT
REACH SVHC	COMPLIANT
HALOGEN-FREE	COMPLIANT
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 3 of 3

RT3215-32.768-7-EXT-TR-NS1

MARKING

R3x7ym

x – Internal Production ID code

y – Year code

m - Month code

YEAR CODE		
Year	Code	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	

ALPHA MONTH CODE TABLE		
Month	Code	
January	A	
February	В	
March	C	
April	D	
May	E	
June	F	
July	G	
August	H	
September	J	
October	K	
November	L	
December	M	

APPROVAL

Drawn By:	KJackson, August 7, 2015
Approved By:	KJackson, August 7, 2015
Revision:	A. Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is required, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI ech does not assume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.