

10W Single/Dual Output DC/DC Converter



FEATURES

- Efficiency up to 87%
- Wide input range, 9V-36V
- Package with Industry Standard Pinout
- Package Dimension:
 25.4 x25.4 x10.2mm (1.0" x1.0" x0.40")(No HSK)
- Over voltage protection, hiccup mode
- Over current protection, hiccup mode
- Positive or Negative Remote ON/OFF
- Without tantalum capacitor inside module
- Operating Temperature range 40°C to +85°C
- Input to Output Isolation: 1600VDC
- RoHS Compliant
- 2 Years Product Warranty
- Heat-sink is option
- UL60950, 2nd Edition, 2011-12-19 Recognized
- EN50155 compliance for Week 1618 datecode afterwards

Security Lab Medical Metro Data Center Telecom Industrial Network

The S24SE/S24DE series is miniature, isolated 10W DC/DC converters with 1600VDC isolation. The S24SE/S24DE family comes with a host of industry-standard features, such as over current protection, over voltage protection, over temperature protection and remote on/off. An optional heatsink is available for more extreme thermal requirements. All models have an ultra-wide 4:1 input voltage range (9V to 36V). With operating temperature of -40°C to +85°C, it is suitable for customers' critical applications, such as process control and automation, transportation, data communication and telecom equipment, test equipment, medical device and everywhere where space on the PCB is critical.

Model List									
Model	Input	Output	Output Current		Input Current		Load	Maxcapacitive	Efficiency
Number	Voltage	Voltage	(typ input voltage) Re		Regulation	Load	(typ.)		
	(Range)		Max.	Min.	@Max. Load	@No Load			@Max. Load
	VDC	VDC	mA	mA	mA(typ.)	mA(typ.)	mV	uF	%
S24SE3R303		3.3V	3000	0	490	35	±10	10000	87%
S24SE05002		5.0V	2000	0	490	35	±10	10000	87%
S24SE120R8	24	12V	830	0	500	30	±12	470	86%
S24SE150R6	(9 ~ 36)	15V	670	0	490	25	±15	470	87%
S24DE120R4		±12V	420	0	490	20	±120	±470	87%
S24DE150R3		±15V	330	0	490	30	±150	±470	87%

Input Characteristics

Item	Model	Min.	Тур.	Max.	Unit			
Input Surge Voltage (100 msec)	All Models			50	VDC			
Input Turn-On Voltage Threshold	All Models	8	8.5	9	VDC			
Input Turn-Off Voltage Threshold	All Models	7	7.5	8	VDC			
Input Under-Voltage Lockout Hysteresis	All Models	0.4	1	1.7	VDC			
Off-Converter Input Current	All Models		6		mA			
Input reflected ripple current	All Models, with 12uH, 20MHz		5	20	mA			
Reverse Polarity Input Current	All Models			0.3	A			
ON/OFF Control, Logic High	All Models	2.4		10	VDC			
ON/OFF Control, Logic Low	All Models	-0.7		0.8	VDC			
Input Filter	All Models		Interna	al PI Filter				




10W Single/Dual Output DC/DC Converter

Output Characteris	stics				
Item	Conditions	Min.	Тур.	Max.	Unit
Output Voltage Accuracy			±1.0	±2.0	%Vo
Output Voltage Balance	Dual Output, Balanced Loads		±1.0	±2.0	%Vo
Line Deculation	Single output		±0.1	±0.2	%Vo
Line Regulation	Dual output		±0.1	±0.5	%Vo
Cross Regulation	Dual output, Asymmetrical Load 25%-100% Full Load		±2	±3	%Vo
Total Output Voltage Range	Over Load, Line and Temperature			±3	%Vo
Ripple & Noise	12V, 15V, ±12V, ±15V		50		mV _{P-P}
Ripple & Noise	3.3V, 5.0V		50		mV _{P-P}
Dynamic load response	50%-75% full load, 0.1A/uS		3		%Vo
Output Over Current Protection	Output Voltage 10% Low, Hiccup	110		160	%lo,max
Short Output Protection	Long Term, Auto-recovery				
Output Over-Voltage Protection	Hiccup, Auto-recovery	115		150	%Vo
Output Trim Range	Single Output	-10		+10	%Vo

General Characteristics									
Item	Conditions	Min.	Тур.	Max.	Unit				
I/O Isolation Voltage (rated)				1600	VDC				
I/O Isolation Resistance		10			MΩ				
I/O Isolation Capacitance			1100		pF				
Switching Frequency			450		KHz				

Environmental Specifications								
Parameter	Conditions	Min.	Max.	Unit				
Operating Temperature Range (with Derating)	Ambient	-40	+85	C°				
Case Temperature (9Vin / 24Vin / 36Vin)			+95 / +105 / +105	C°				
NTC Shutdown Temperature			+125	C°				
Storage Temperature Range		-55	+125	C°				
Humidity (non condensing)			95	% rel. H				
Cooling	Natural Convection							



Notes


Specifications typical at Ta=+25°C, resistive load, nominal input voltage and rated output current unless otherwise noted. 1

- 2 Ripple & Noise measurement bandwidth is 0-20MHz, with 10µF, tantalum capacitor and 1µF ceramic capacitor.
- 3 All DC/DC converters should be externally fused at the front end for protection.
- 4 Specifications are subject to change without notice.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24SE3R303, 9-36VIN, 3.3V/3A



Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (4ms/div). Top Trace: Vout; 1V/div; Bottom Trace: ON/OFF input: 5V/div.




Output voltage ripple at nominal input voltage and max load current (5mV/div, 2us/div)

Load cap: 10μ F, tantalum capacitor and 1μ F ceramic capacitor. Bandwidth: 20 MHz.

DS_ S24SE/S24DE 10W _07152020



Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (4ms/div). Top Trace: Vout; 1V/div; Bottom Trace: input voltage: 20V/div.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24SE05002, 9-36VIN, 5.0V/2A




Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (10ms/div). Top Trace: Vout; 2V/div; Bottom Trace: ON/OFF input: 5V/div.



Output voltage ripple at nominal input voltage and max load current (20 mV/div, 2us/div) Load cap: 10μ F, tantalum capacitor and 1μ F ceramic capacitor. Bandwidth: 20 MHz.



Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (10 ms/div). Top Trace: Vout; 2V/div; Bottom Trace: input voltage: 8V/div.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24SE120R8, 9-36VIN, 12V/0.83A




Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (4ms/div). Top Trace: Vout; 5V/div; Bottom Trace: ON/OFF input: 5V/div.



Output voltage ripple at nominal input voltage and max load current (10 mV/div, 2us/div) Load cap: 10μ F, tantalum capacitor and 1μ F ceramic capacitor. Bandwidth: 20 MHz.



Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (4 ms/div). Top Trace: Vout; 5V/div; Bottom Trace: input voltage: 8V/div.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24SE150R6, 9-36VIN, 15V/0.67A



Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (4ms/div). Top Trace: Vout; 5V/div; Bottom Trace: ON/OFF input: 5V/div.




Output voltage ripple at nominal input voltage and max load current (4mV/div, 2us/div)

Load cap: 10μ F, tantalum capacitor and 1μ F ceramic capacitor. Bandwidth: 20 MHz.



Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (4ms/div). Top Trace: Vout; 5V/div; Bottom Trace: input voltage: 8V/div.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24DE120R4, 9-36VIN, ±12V/0.42A



Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (10ms/div). Top two Traces: Vout; 10V/div; Bottom Trace: ON/OFF input: 5V/div.




Output voltage ripple at nominal input voltage and max load current Top trace +12V, 10 mV/div, Bottom trace -12V, 20mV/div, 2us/div.

Load cap: 10 μF tantalum capacitor and 1 μF ceramic capacitor. Bandwidth: 20 MHz.



Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (10 ms/div). Top two Traces: Vout; 10V/div; Bottom Trace: input voltage: 15V/div.




10W Single/Dual Output DC/DC Converter


ELECTRICAL CHARACTERISTICS CURVES - S24DE150R3, 9-36VIN, ±15V/0.33A



Efficiency vs. load current for various input voltage at 25°C.




Turn-on transient at full load current (10ms/div). Top two traces: Vout; 10V/div; Bottom Trace: ON/OFF input: 5V/div.




Output voltage ripple at nominal input voltage and max load current Top trace +15V, 10 mV/div, Bottom trace -15V, 20mV/div, 2us/div.

Load cap: 10μ F, tantalum capacitor and 1μ F ceramic capacitor. Bandwidth: 20 MHz.



Power dissipation vs. load current at 25°C.



Turn-on transient at full load current (10 ms/div). Top two traces: Vout; 10V/div; Bottom Trace: input voltage: 15V/div.




10W Single/Dual Output DC/DC Converter

DESIGN CONSIDERATIONS

Input Source Impedance


The impedance of the input source connecting to the DC/DC power modules will interact with the modules and affect the stability. A low ac-impedance input source is recommended. If the source inductance is more than a few μ H, we advise a 47 μ F electrolytic capacitor mounted close to the input of the module to improve the stability.

Input Reflected Ripple Current




Test set-up diagram showing measurement points for Input Terminal Ripple Current and Input Reflected Ripple Current.

Measured input reflected-ripple current with a simulated source Inductance (LTEST) of 12 μ H. Capacitor Cs offset possible battery impedance.




Input Terminal Ripple Current, ic, at full rated output current and nominal input voltage with 12μ H source impedance and 100μ F electrolytic capacitor (20 mA/div, 2us/div).



Input reflected ripple current, is, through a 12µH source inductor at nominal input voltage and rated load current (5 mA/div, 2us/div)

Output Ripple Noise



Output voltage ripple test setup.

Load capacitance: 1μ F ceramic capacitor and 10μ F tantalum capacitor. Bandwidth: 20 MHz. Scope measurements should be made using a BNC cable (length shorter than 20 inches). Position the load between 51 mm to 76 mm (2 inches to 3 inches) from the module.




10W Single/Dual Output DC/DC Converter


DESIGN CONSIDERATIONS



Delta's DC/DC power modules are designed to operate in a wide variety of systems and applications. For design assistance with EMC compliance and related PWB layout issues, please contact Delta's technical support team. An external input filter module is available for easier EMC compliance design. Below is the reference design for an input filter to pass EN55022 (VDE0878) class A (both q. peak and average).








Test Result:

At T = +25°C, Typical input voltage and full load. Green is quasi peak mode; Blue is average mode.



Recommended PCB Layout

It is suggested to use multiple layers PCB and large size copper on system board which connects to pins of module, that can achieve better thermal performance.

FEATURES DESCRIPTIONS Over-Current Protection

The modules include an internal output over-current protection circuit, which will endure current limiting for an unlimited duration during output overload. If the output current exceeds the OCP set point, the modules will shut down (hiccup mode).

The modules will try to restart after shutdown. If the overload condition still exists, the module will shut down again. This restart trial will continue until the overload condition is corrected.

Over-Voltage Protection

The modules include an internal output over-voltage protection circuit, which monitors the voltage on the output terminals. If this voltage exceeds the over-voltage set point, the modules will shut down, and then restart after a hiccup-time (hiccup mode).

If latch mode is needed, please contact with Delta.

Over-Temperature Protection

The over-temperature protection consists of circuitry that provides protection from thermal damage. If the temperature exceeds the over-temperature threshold the module will shut down. The module will restart after the temperature is within specification.

Remote On/Off


The remote on/off feature on the module can be either negative or positive logic depend on the part number options on the last page.

- For Negative logic version, turns the module on during a external logic low and off during a logic high. If the remote on/off feature is not used, please short the on/off pin to Vi (-).
- For Postive logic version, turns the modules on during a external logic high and off during a logic low. If the remote on/off feature is not used, please leave the on/off pin to floating.

Remote on/off can be controlled by an external switch between the on/off terminal and the Vi (-) terminal. The switch can be an open collector or open drain.



10W Single/Dual Output DC/DC Converter



Remote on/off implementation

Output Voltage Adjustment (TRIM)


Only single output modules have output adjust function.

To increase the output voltage set point, connect an external resistor between the TRIM pin and the Vout(-).

To decrease the output voltage set point, connect an external resistor between the TRIM pin and the Vout(+).

The maximum adjust range is $\pm 10\%$, the TRIM pin should be left open if this feature is not used.


For 3.3V single output(Kohm):




For 5V single output (Kohm):



For 12V single output (Kohm):



For 15V single output (Kohm):



For example:

When need trim up to 3.4V, then the external resistor should be 100Kohm between trim pin and Vout- pin. When need trim down to 3.1V, then the external resistor should be 40Kohm between trim pin and Vout+ pin.


THERMAL CONSIDERATIONS

Thermal de-rating curve is a standard for customer to make thermal evaluation and make sure the module's components are operated under allowed temperature. The module's cooling condition is natural convection. In thermal de-rating curve, if we know the module's input voltage and output power we can find the allowed maximum ambient temperature.

The module's case temperature is a reference to make thermal evaluation. If the case temperature exceed the allowed maximum value, the moldule may probably have thermal issue.



10W Single/Dual Output DC/DC Converter



- 1. add heat sink to help heat dissipation and increase reliability of convert operating at high ambient temperature
- 2. please refer derating curve while upgrate the operating temperature of converter




Application notice:

For modules with through-hole pins, they are intended for wave soldering assembly onto system boards; please do not subject such modules through reflow temperature profile.

Recommended layout refer below







10W Single/Dual Output DC/DC Converter

Part	Part Numbering System										
S	24	S	E	050	02	Р	D	F	А		
Form factor	Input voltage	Number of output	Product series	Output voltage	Output current	On/off logic	Pin length		Option Code		
S	24 - 9~36V	S - Single D - Dual	E - Series No.	050 - 5.0V	02 - 2A	N - Negative P - Positive	D - 0.24" T - 0.22" R - 0.17"	F - RoHS 6/6 (Lead Free)	A - Standard. (with metal case) H - With heat sink		

CONTACT: <u>www.deltaww.com/dcdc</u>

USA: Telephone: East Coast: 978-656-3993 West Coast: 510-668-5100 Fax: (978) 656 3964 Email: dcdc@deltaww.com

Europe: Phone: +31-20-655-0967 Fax: +31-20-655-0999 Asia & the rest of world: Telephone: +886 3 4526107 ext 6220~6226 Fax: +886 3 4513485

WARRANTY

Delta offers a two (2) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.