SIEMENS

Data sheet

US2:17CUD92BS



Non-reversing motor starter, Size 0, Three phase full voltage, Solid-state overload relay, OLR amp range 5.5-22A, 24VDC coil, Combination type, 30A non-fusible disconnect, Enclosure NEMA type 1, Indoor general purpose use, Standard width enclosure

Figuresin	nilar
-----------	-------

product brand name	Class 17 & 25
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect
special product feature	ESP200 overload relay
General technical data	
Height x Width x Depth [in]	24 × 11 × 8 in
touch protection against electrical shock	(NA for enclosed products)
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
 during storage 	-22 +149 °F
during operation	-4 +104 °F
ambient temperature	
 during storage 	-30 +65 °C
during operation	-20 +40 °C
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	3 hp
• at 220/230 V rated value	3 hp
• at 460/480 V rated value	0 hp
 at 575/600 V rated value 	0 hp
Contactor	
size of contactor	NEMA controller size 0
number of NO contacts for main contacts	3
operational current at AC at 600 V rated value	18 A
mechanical service life (switching cycles) of the main contacts typical	1000000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	0
number of NO contacts at contactor for auxiliary contacts	1
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)
Coil	
type of voltage of the control supply voltage	DC
control supply voltage	
 at DC rated value 	24 V
holding power at AC minimum	0 W
apparent pick-up power of magnet coil at AC	163 VA
apparent holding power of magnet coil at AC	5.5 VA

operating range factor control supply voltage rated value of magnet coil	0.85 1.1	
percental drop-out voltage of magnet coil related to the input voltage	25 %	
ON-delay time	21 21 ms	
OFF-delay time	11 11 ms	
Overload relay		
product function		
 overload protection 	Yes	
phase failure detection	Yes	
asymmetry detection	Yes	
ground fault detection	Yes	
• test function	Yes	
external reset	Yes	
reset function	Manual, automatic and remote	
trip class	CLASS 5 / 10 / 20 (factory set) / 30	
adjustable current response value current of the current- dependent overload release	5.5 22 A	
make time with automatic start after power failure maximum	3 s	
relative repeat accuracy	1 %	
product feature protective coating on printed-circuit board	Yes	
number of NC contacts of auxiliary contacts of overload relay	1	
number of NO contacts of auxiliary contacts of overload relay	1	
operational current of auxiliary contacts of overload relay		
• at AC at 600 V	5 A	
• at DC at 250 V	1 A	
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)		
 with single-phase operation at AC rated value 	600 V	
 with multi-phase operation at AC rated value 	300 V	
Disconnect Switch		
response value of switch disconnector	30A / 600V	
design of fuse holder	non-fusible	
operating class of the fuse link	non-fusible	
Enclosure		
degree of protection NEMA rating	1	
design of the housing	indoors, usable on a general basis	
Mounting/wiring		
mounting position	vertical	
fastening method	Surface mounting and installation	
type of electrical connection for supply voltage line-side	Box lug	
tightening torque [lbf·in] for supply	35 35 lbf·in	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)	
temperature of the conductor for supply maximum permissible	75 °C	
material of the conductor for supply	AL or CU	
type of electrical connection for load-side outgoing feeder	Screw-type terminals	
tightening torque [lbf·in] for load-side outgoing feeder	20 20 lbf·in	
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)	
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C	
material of the conductor for load-side outgoing feeder	AL or CU	
type of electrical connection of magnet coil	Screw-type terminals	
tightening torque [lbf·in] at magnet coil	5 12 lbf·in	
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)	

75 °C		
CU		
Screw-type terminals		
10 15 lbf·in		
1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)		
75 °C		
CU		
Screw-type terminals		
7 10 lbf·in		
2x (20 14 AWG)		
75 °C		
CU		
10kA@600V (Class H or K); 100kA@600V (Class R or J)		
NEMA ICS 2; UL 508; CSA 22.2, No.14		
Further information Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17CUD92BS Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92BS Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17CUD92BS⟨=en Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92BS/certificate		

last modified:

1/25/2022 🖸