## **SIEMENS**

**US2:83DUC95WG Data sheet** 



Duplex starter w/o alternator, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 3-12A, 190-220/220-240V 50/60Hz coil, Non-combination type, Encl NEMA type 4X 304 S-Steel, Water/dust tight

| product brand name      | Class 83                             |
|-------------------------|--------------------------------------|
| design of the product   | Duplex controller without alternator |
| special product feature | ESP200 overload relay                |
| General technical data  |                                      |

| General technical data                                       |                          |
|--|--------------------------|
| weight [lb]  | 40 lb                    |
| Height x Width x Depth [in]                                  | 20 × 16 × 6 in           |
| touch protection against electrical shock                    | NA for enclosed products |
| installation altitude [ft] at height above sea level maximum | 6560 ft                  |
| ambient temperature [°F]                                     |                          |
| <ul> <li>during storage</li> </ul>                           | -22 +149 °F              |
| during operation   | -4 +104 °F               |
| ambient temperature  |                          |
| <ul> <li>during storage</li> </ul>                           | -30 +65 °C               |
| <ul> <li>during operation</li> </ul>                         | -20 +40 °C               |
|  | 110 4                    |

| • during operation                                       | -20 140 0 |
|--|-----------|
| country of origin  | USA       |
| Horsepower ratings                                       |           |
| yielded mechanical performance [hp] for 3-phase AC motor |           |
| <ul><li>at 200/208 V rated value</li></ul>               | 2 hp      |
| • at 220/230 V rated value                               | 2 hp      |
|  |           |

| <ul> <li>at 460/480 V rated value</li> </ul> | 5 hp                   |
|--|------------------------|
| <ul> <li>at 575/600 V rated value</li> </ul> | 5 hp                   |
| Contactor                                    |                        |
| size of contactor                            | NEMA controller size 1 |
| number of NO contacts for main contacts      | 3                      |

| number of the contacts for main contacts                                | · ·      |
|---|----------|
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V    |
| operational current at AC at 600 V rated value                          | 27 A     |
| mechanical service life (switching cycles) of the main contacts typical | 10000000 |
| Auvilians contact   |          |

| contacts typical  |                                     |
|---|-------------------------------------|
| Auxiliary contact   |                                     |
| number of NC contacts at contactor for auxiliary contacts         | 0                                   |
| number of NO contacts at contactor for auxiliary contacts         | 1                                   |
| number of total auxiliary contacts maximum                        | 8                                   |
| contact rating of auxiliary contacts of contactor according to UL | 10A@600VAC (A600), 5A@600VDC (P600) |
| Coil  |                                     |
| type of voltage of the control supply voltage                     | AC                                  |
| control supply voltage  |                                     |

Со

| at DO astad value  | 0 01/  |
|--|--|
| at DC rated value     at AC at 50 Hz rated value   | 0 0 V  |
| at AC at 50 Hz rated value   | 190 220 V                                      |
| at AC at 60 Hz rated value  holding power at AC minimum.   | 220 240 V<br>8.6 W                             |
| holding power at AC minimum apparent pick-up power of magnet coil at AC                            | 218 VA   |
| apparent holding power of magnet coil at AC  | 25 VA  |
| operating range factor control supply voltage rated value  | 0.85 1.1                                       |
| of magnet coil   | 0.00 1.1                                       |
| percental drop-out voltage of magnet coil related to the input voltage                             | 50 %   |
| ON-delay time  | 19 29 ms                                       |
| OFF-delay time   | 10 24 ms                                       |
| Overload relay   |  |
| product function   |  |
| <ul> <li>overload protection</li> </ul>  | Yes  |
| <ul> <li>phase failure detection</li> </ul>  | Yes  |
| <ul> <li>asymmetry detection</li> </ul>  | Yes  |
| ground fault detection   | Yes  |
| <ul><li>test function</li></ul>  | Yes  |
| external reset   | Yes  |
| reset function   | Manual, automatic and remote                   |
| adjustable current response value current of the current-<br>dependent overload release            | 3 12 A   |
| tripping time at phase-loss maximum  | 3 s  |
| relative repeat accuracy   | 1 %  |
| product feature protective coating on printed-circuit board  | Yes  |
| number of NC contacts of auxiliary contacts of overload relay                                      | 1  |
| number of NO contacts of auxiliary contacts of overload relay                                      | 1  |
| operational current of auxiliary contacts of overload relay  |  |
| • at AC at 600 V   | 5 A  |
| ● at DC at 250 V   | 1 A  |
| contact rating of auxiliary contacts of overload relay according to UL                             | 5A@600VAC (B600), 1A@250VDC (R300)             |
| insulation voltage (Ui)  |  |
| with single-phase operation at AC rated value  | 600 V  |
| <ul> <li>with multi-phase operation at AC rated value</li> </ul>                                   | 300 V  |
| Enclosure  |  |
| degree of protection NEMA rating of the enclosure  | NEMA 4x 304 stainless steel enclosure          |
| design of the housing  | dustproof, waterproof & resistant to corrosion |
| Mounting/wiring  |  |
| mounting position  | Vertical                                       |
| fastening method   | Surface mounting and installation              |
| type of electrical connection for supply voltage line-side   | Screw-type terminals                           |
| tightening torque [lbf-in] for supply  | 35 35 lbf-in                                   |
| type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded   | 1x (14 2 AWG)                                  |
| temperature of the conductor for supply maximum permissible  | 75 °C  |
| material of the conductor for supply   | AL or CU                                       |
| type of electrical connection for load-side outgoing feeder  | Screw-type terminals                           |
| tightening torque [lbf-in] for load-side outgoing feeder   | 35 35 lbf-in                                   |
| type of connectable conductor cross-sections at AWG  | 1x (14 2 AWG)                                  |
| cables for load-side outgoing feeder single or multi-<br>stranded                                  | 1A (17 2 AWO)                                  |
| temperature of the conductor for load-side outgoing feeder maximum permissible                     | 75 °C  |
| material of the conductor for load-side outgoing feeder  | AL or CU                                       |
| type of electrical connection of magnet coil   | Screw-type terminals                           |
| tightening torque [lbf·in] at magnet coil  | 5 12 lbf·in                                    |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded | 2x (16 12 AWG)                                 |

| temperature of the conductor at magnet coil maximum permissible  | 75 °C   |
|--|---|
| material of the conductor at magnet coil   | CU  |
| type of electrical connection at contactor for auxiliary contacts  | Screw-type terminals                                |
| tightening torque [lbf·in] at contactor for auxiliary contacts   | 10 15 lbf·in  |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi-stranded      | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)         |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible   | 75 °C   |
| material of the conductor at contactor for auxiliary contacts  | CU  |
| type of electrical connection at overload relay for auxiliary contacts   | Screw-type terminals                                |
| tightening torque [lbf·in] at overload relay for auxiliary contacts  | 7 10 lbf·in   |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi-stranded | 2x (20 14 AWG)                                      |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                    | 75 °C   |
| material of the conductor at overload relay for auxiliary contacts   | CU  |
| Short-circuit current rating   |   |
| design of the fuse link for short-circuit protection of the main circuit required  | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip   | Thermal magnetic circuit breaker                    |
| breaking capacity maximum short-circuit current (Icu)  |   |
| • at 240 V   | 14 kA   |
| • at 480 V   | 10 kA   |
| • at 600 V   | 10 kA   |
| certificate of suitability   | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |
| Further information  |   |

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:83DUC95WG

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:83DUC95WG

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:83DUC95WG&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:83DUC95WG/certificate

| ast modified: | 1/25/2022 🖸 |
|---------------|-------------|
|               |             |