


HLD CONNECTOR



1.0 mm pitch/Disconnectable Crimp style connectors



Developed for PDP, LCD or small electronics equipment.

This is a dual-row small crimp type connector with a secure locking system or without-designed for different applications. The PC board layout is compatible with that of existing SHD connector, which allows for replacement of the above existing connector.

- Secure housing lock structure (for locking type)
- Prevent deformation of contacts
- A contact lock structure
- Strong structure against external force

Specifications —

- Current rating: 1.0 A AC/DC (AWG #28)
- Voltage rating: 50 V AC/DC
- Temperature range: -25°C to +85°C

(including temperature rise in applying electrical current)

• Contact resistance: Initial value/ 30 m Ω max.


After environmental tests/ 40 m Ω max.


- Insulation resistance: 100 M Ω min.
- Withstanding voltage: 500 VAC/minute
- * In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.

Standards -

Recognized E60389

PC board layout and Assembly layout






Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative: ± 0.1 mm for all centers. The dimensions above should serve as a guideline. Contact JST for details.

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	O'ty/rool
MIOGEL ING.	mm ²	AWG #	ilisulation O.D. (IIIII)	Q ty/reer
SSHL-003GA1-P0.2	0.032 to 0.08	32 to 28	0.4 to 0.8	41,000

Material and Finish

Phosphor bronze, nickel-undercoated, Mating part; gold-plated.


RoHS2 compliance

Contact	Crimping	Applicator		
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies
SSHL-003GA1-P0.2	AP-K2N	MKS-L-10-3	MK/SSH/L-003-02	APLMK SSH/L003-02

Note: Contact JST for fully automatic crimping applicator.

SHLD CONNECTOR

Housing



No. of	Model No.	Dir	Q'ty/bag		
circuits	Widdel No.	Α	В	С	Q ty/bag
20	SHLDP-20V-S(B)	9.0	11.4	13.0	3,500
30	SHLDP-30V-S(B)	14.0	16.4	18.0	2,500
40	SHLDP-40V-S(B)	19.0	21.4	23.0	2,000
50	SHLDP-50V-S(B)	24.0	26.4	28.0	1,500

Material and Finish

PBT, UL94V-0, natural (white)

RoHS2 compliance

With secure lock type


No. of		Model No.	Dir	O't /b = =:			
	circuits	S Wiodel No.	Α	В	C	Q'ty/bag	
	20	SHLDP-20V-S-1 (B)	9.0	14.7	15.7	3,000	
	30	SHLDP-30V-S-1 (B)	14.0	19.7	20.7	2,000	
	40	SHLDP-40V-S-1 (B)	19.0	24.7	25.7	1,500	
	50	SHLDP-50V-S-1 (B)	24.0	29.7	30.7	1,200	

Material and Finish

PBT, UL94V-0, natural (white)

RoHS2 compliance

Header



No. of	Model No.		Dimensions (mm)		Q'ty/reel	
circuits	Top entry type	Side entry type	Α	В	Top type	Side type
20	BM20B-SHLDS-G-TFT	SM20B-SHLDS-G-TF	9.0	13.0	1,400	1,000
30	BM30B-SHLDS-G-TFT	SM30B-SHLDS-G-TF	14.0	18.0	1,400	1,000
40	BM40B-SHLDS-G-TFT	SM40B-SHLDS-G-TF	19.0	23.0	1,400	1,000
50	BM50B-SHLDS-G-TFT	SM50B-SHLDS-G-TF	24.0	28.0	1,400	1,000

Material and Finish


Contact: Phosphor bronze, nickel-undercoated, gold-plated Wafer: PA, UL94V-0, natural (ivory)


Solder tab: Brass, copper-undercoated, tin-plated (reflow treatment)

RoHS2 compliance This product displays (LF)(SN) on a label.

Model number allocation

Contact Housing





Header

