INDUCTORS



Inductors for power circuits **Wound ferrite SLF-H series (for automotive)**









SLF7045-H type














FEATURES

- Magnetic shield type wound inductor for power circuits.
- O Product lineup allows for various usages
- Operating temperature range: -40 to +125°C (including self-temperature rise)

APPLICATION

- Outcomotive-related equipment (ECM, airbags, headlights, electronic power steering, meters, ABS, other)
- O Application guides: Automotive (xEV)

■ PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

L		L measuring frequency	DC resistance	Rated curre	ent*		Part No.
				Isat	Isat	Itemp	
(μH)	Tolerance	(kHz)	(Ω)	(A)max.	(A)typ.	(A)typ.	
3.3	±20%	100	0.028±20%	2.20	6.30	2.30	SLF7045T-3R3M2R2-H
4.7	±20%	100	0.031±20%	2.10	5.10	2.10	SLF7045T-4R7M2R1-H
6.8	±20%	100	0.039±20%	1.90	4.70	2.04	SLF7045T-6R8M1R9-H
10	±20%	100	0.047±20%	1.80	3.70	1.81	SLF7045T-100M1R8-H
15	±20%	100	0.068±20%	1.50	2.90	1.46	SLF7045T-150M1R5-H
22	±20%	100	0.082±20%	1.30	2.50	1.25	SLF7045T-220M1R3-H
33	±20%	100	0.120±20%	1.10	2.00	1.11	SLF7045T-330M1R1-H
47	±20%	100	0.180±20%	0.90	1.70	0.93	SLF7045T-470MR90-H
68	±20%	100	0.270±20%	0.75	1.40	0.76	SLF7045T-680MR75-H
100	±20%	100	0.390±20%	0.60	1.10	0.61	SLF7045T-101MR60-H
150	±20%	100	0.550±20%	0.50	1.00	0.54	SLF7045T-151MR50-H
220	±20%	100	0.830±20%	0.40	0.70	0.43	SLF7045T-221MR40-H
330	±20%	100	1.15±20%	0.35	0.60	0.37	SLF7045T-331MR35-H
470	±20%	100	1.80±20%	0.31	0.40	0.31	SLF7045T-471MR31-H

^{*} Isat(max.): When based on the inductance change rate (10% below the initial value) Isat(typ.): When based on the inductance change rate (30% below the initial value) Itemp: When based on the temperature increase (temperature increase of 20°C by self heating)

Measurement equipment

• •		
Measurement item	Product No.	Manufacturer
L	4194A	Keysight Technologies
DC resistance	VP-2941A	Panasonic
Rated current Isat	4284A+42841A+42842C	Keysight Technologies


^{*} Equivalent measurement equipment may be used.





SLF7045-H type

L FREQUENCY CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer		
4294A	Keysight Technologies		

^{*} Equivalent measurement equipment may be used.



SLF7045-H type

■INDUCTANCE VS. DC BIAS CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
4284A+42841A+42842C	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



SLF7045-H type


■ SHAPE & DIMENSIONS



Dimensions in mm

■ PACKAGING STYLE

□REEL DIMENSIONS




Dimensions in mm

RECOMMENDED LAND PATTERN




Dimensions in mm

TAPE DIMENSIONS



Туре	Α	В	K
SLF7045-H	7.4	7.6	4.8

■ RECOMMENDED REFLOW PROFILE



□PACKAGE QUANTITY

Package quantity	1000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating	Storage	Individual
temperature range*	temperature range**	weight
-40 to +125 °C	−40 to +125 °C	0.6 g

^{*} Operating temperature range includes self-temperature rise.

^{**} The storage temperature range is for after the assembly.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

⚠ REMINDERS
The storage period is less than 6 months. Be sure to follow the storage conditions (temperature: 5 to 30°C, humidity: 10 to 75% RH of ess). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperatur does not exceed 150°C.
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermodesign.
Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
Do not expose the products to magnets or magnetic fields.
Do not use for a purpose outside of the contents regulated in the delivery specifications.
The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quatty require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to societ

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

(3) Medical equipment

person or property.

- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions