

R75TW333050L3J

Aliases (75TW333050L3J)

R75, Film, Metallized Polypropylene, General Purpose, 0.33 uF, 5%, 1600 VDC, 85°C, Lead Spacing = 37.5mm



Click [here](#) for the 3D model.

Dimensions

L	41.5mm +0.3/-0.7mm
H	19mm +0.1/-0.7mm
T	24mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	108

General Information

Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	19.3 g
Miscellaneous	Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C.

Specifications

Capacitance	0.33 uF
Capacitance Tolerance	5%
Voltage AC	650 VAC
Voltage DC	1600 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	750 V/us
Resistance	8.199 mOhms (100kHz)
Ripple Current	10.33 Amps (100kHz 85C), 248 Amps (Peak)
Inductance	20 nH