





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
02	△△	料號變更	2009.04.27	彭思城
03	△△	依業務要求增加包裝配方	2009.12.28	謝金發
04	△△	依上級要求變更圖號	2011.07.14	李芳忠



Specifications  
 Current Rating: 3Amp  
 Insulation Resistance: 1000MΩMin.  
 Dielectric Withstanding Voltage: 600VAC  
 Contact Resistance: 20mΩMax.  
 Operating Temperature: -40°C to +105°C  
 Materials  
 Contact Material: Phosphor Bronze  
 Insulator Material: Thermoplastic, UL 94V-0  
 PBT or the equivalent material  
 All materials must meet Greenconn  
 requirement for environment protection.



Recommended P.C.Board  
 Layout  
 (Tolerance: ±0.05)



### Ordering Information

G PHA204 - XX XX A 001 A 1 A X

No. of Pins per Row: 03~32  
 Standard Plating: 02=Gold Flash, 01=Tin, Selective Plating: 05=Gold Flash/Tin  
 Color: 1=Black  
 Standard Packing: △ B=Tray, Selective Packing: A=Box, C=Tube

格菱股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2011.07.14	DWG. NO. △△	TITLE: 2.54 BOX HEADER DUAL ROWS DIP TYPE BASE 9.10H
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2011.07.14	GPHA204-CA1AA	
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2011.07.14	PART NO. △	
.XX*±2.0°	.XX±0.15	APPROVED: cc_Li	DATE: 2011.07.14	GPHA204-XXXX A001A1AX	
.XXX*±1.0°	.XXX±0.10				

REV.	UNIT.	SCALE.	PAGE.	Symbol
04	mm	2:1	1/1	⊕