




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01		INITIAL RELEASE.	06-13-05	XIAO PING
02	△	變更塑膠用料	29.05.2008	周禮軍
03	△	Change Part NO.	2009.02.23	莫芝蘭
04	△	變更圖號與注解	2011.07.25	黃明霞

Specifications


Current Rating: 1Amp
 Insulation Resistance: 1000MΩ Min.
 Dielectric Withstanding: 300V AC/DC
 Contact Resistance: 20mΩ Max.
 Operating Temperature: -40°C to +105°C

Materials


Contact Material: Phosphor bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn requirement for environment protection



Recommended P.C.Board
 Hole Layout



Ordering Information



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X. ±5.0°	X. ±0.30
.X ±3.0°	.X ±0.25
.XX ±2.0°	.XX ±0.15
.XXX ±1.0°	.XXX ±0.10

DESIGN: 黃明霞	DATE: 2011.07.25
CHECKED: 李新華	DATE: 2011.07.25
AUDITED: LINK	DATE: 2011.07.25

DWG. NO.	△△△ CSEB202-CATCA
PART NO.	△ CSEB202-XXXX A001C1AX

TITLE.	1.27 PIN HEADER DUAL ROWS R/A TYPE BASE 4.40H
--------	---

REV.	UNIT.	SCALE.	PAGE.	Symbol
04	mm	1:1	1/1	⊕