



Click [here](#) for the 3D model.

Dimensions

L	41.5mm +0.3/-0.7mm
H	19mm +0.1/-0.7mm
T	24mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	108

General Information

Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	20.4 g
Miscellaneous	Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C.

Specifications

Capacitance	2.2 uF
Capacitance Tolerance	5%
Voltage AC	250 VAC
Voltage DC	630 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.06% 1kHz, 0.08% 10kHz
Insulation Resistance	13.6364 GOhms
Max dV/dt	90 V/us
Resistance	7.234 mOhms (100kHz)
Ripple Current	11 Amps (100kHz 85C), 198 Amps (Peak)
Inductance	20 nH