



SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
4. Contact Resistance: $20\text{m}\Omega$ Max
5. Insulation Resistance: $1000\text{m}\Omega$ Min
6. Withstanding Voltage: 800V AC/minute
7. Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-PHD-2x2AW	2.00	6.00
3	HC-PHD-2x3AW	4.00	8.00
4	HC-PHD-2x4AW	6.00	10.00
5	HC-PHD-2x5AW	8.00	12.00
6	HC-PHD-2x6AW	10.00	14.00
7	HC-PHD-2x7AW	12.00	16.00
8	HC-PHD-2x8AW	14.00	18.00
9	HC-PHD-2x9AW	16.00	20.00
10	HC-PHD-2x10AW	18.00	22.00
11	HC-PHD-2x11AW	20.00	24.00
12	HC-PHD-2x12AW	22.00	26.00
13	HC-PHD-2x13AW	24.00	28.00
14	HC-PHD-2x14AW	26.00	30.00
15	HC-PHD-2x15AW	28.00	32.00
16	HC-PHD-2x16AW	30.00	34.00
17	HC-PHD-2x17AW	32.00	36.00
18	HC-PHD-2x18AW	34.00	38.00
19	HC-PHD-2x19AW	36.00	40.00
20	HC-PHD-2x20AW	38.00	42.00

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM	TOL	审核 CHECK		产品名称 TITLE		PHD (2.0)双排 定位弯针	版本 REV.	A
			X.X	±0.30	批准 APPROVAL		产品料号 PART NO.		HC-PHD-2xNAW	单位 UNITS	mm
1 初版发行			X.XX	±0.20	比例 SCALE		材料 MATERIAL			页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection						
			Angle	±3.0°							