

5W, 15V Surface Mount Zener Diode

FEATURES

- AEC-Q101 qualified
- Ideal for automated placement
- Glass passivated chip junction
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

• For general purpose regulation and protection applications

MECHANICAL DATA

• Case: DO-214AB (SMC)

Molding compound meets UL 94V-0 flammability rating
Terminal: Matte tin plated leads, solderable per J-STD-002

Meet JESD 201 class 2 whisker test
Polarity: Indicated by cathode band
Weight: 0.260g (approximately)

KEY PARAMETERS			
PARAMETER	VALUE	UNIT	
V_Z	15	V	
P_D	5 W		
T _{J MAX}	150 °C		
Package	DO-214AB (SMC)		
Configuration	Single die		









DO-214AB (SMC)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)				
PARAMETER	SYMBOL	VALUE	UNIT	
Steady state power dissipation at T _L = 75°C	P_{D}	5	W	
Junction temperature	T_J	-55 to +150	°C	
Storage temperature	T _{STG}	-55 to +150	°C	

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be attached.

THERMAL PERFORMANCE				
PARAMETER	SYMBOL	TYP	UNIT	
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	55	°C/W	





ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)								
Part number (Note 1)	Marking code	Regulator Voltage (Note 2)	Test Current	Maximum Dynamic Impedance	Maximum Reverse Current	I _R lest	Maximum Regulator Current	Maximum Dynamic Knee Impedance
(Note 1)	code	$V_z@I_z$	I _Z	Z_Z	I _R	V_R	I_{ZM}	Z _{ZK} @1mA
		V	mA	Ω	μA	V	mA	Ω
1SMC5352H	352B	15	75	2.5	1.0	11.5	315	75

Notes:

- 1. Tolerance and voltage regulation designation. The type number listed indicates a tolerance of 5%.
- 2. Zener voltage (V_Z) measurement Nominal Zener voltage is measured with the device junction in thermal equilibrium with ambient temperature 25° C

ORDERING INFORMATION				
ORDERING CODE PACKAGE PACKING				
1SMC5352H	DO-214AB (SMC)	3,000 / Tape & Reel		



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.1 Effect Of Zener Current

1000

(C) DANAMIC IMPEDANCE IVA

100


100

Iz. ZENER TEST CURRENT (mA)

LEAD TEMPERATURE (°C)

Fig.2 Steady State Power Derating


Fig.3 Typical Junction Capacitance






PACKAGE OUTLINE DIMENSIONS


DO-214AB (SMC)





DIM	DIM. Unit (m		nm) Unit (inch)		
DIN.	Min.	Max.	Min.	Max.	
Α	2.00	2.62	0.079	0.103	
A1	0.10	0.20	0.004	0.008	
b	2.90	3.20	0.114	0.126	
С	0.15	0.31	0.006	0.012	
D	5.59	6.22	0.220	0.245	
E	7.75	8.13	0.305	0.320	
E1	6.60	7.11	0.260	0.280	
L	1.00	1.60	0.039	0.063	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	3.30	0.130
В	2.50	0.098
С	6.90	0.272
D	4.40	0.173
E	9.40	0.370

MARKING DIAGRAM



P/N = Marking Code G = Green Compound

YW = Date Code F = Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.