# 

Acoustic Product Specification

#### Product Number: PT-1109S



Release | Revision: A/2019

#### CONTENTS

This document contains the technical specifications for the piezo audio transducer.

Page 1 Specifications

Mechanical Characteristics

Page 2 Environment Test

**Reliability Test** 

Page 3 Measuring Method (Speaker Mode)

Soldering Condition

Page 4

Page 5 Packing

Material Table

Specifications			
ltem	Unit	Specification	Condition
Rated Voltage	Vp-р	5.0	
Operating Voltage	Vp-p	1.0 ~ 25.0.	0V ↓ ↓ >Vp-p
Mean Current	mA	4.5 Max.	At rated voltage
Sound Output	dB	73	At 10cm / 5Vp-p,
Capacitance at 30Hz	pF	12000 ±30%	
Rated Frequency	Hz	4100±500	Vp-p=Duty, square wave
Operating Temp	°C	-40 ~ +85	
Storage Temp	°C	-40 ~ +85	
Dimension	mm	11.0 × 9.0× H1.7	
Weight	gram	0.25	
Housing Material		LCP(Black)	
Terminal		SMD Type (Plating Sn)	See dimension
Environmental Protection Regulation		RoHS	
Test condition:			

Temperature: +25±2 °C

Related humidity: 65±5% Pressure: 86~106KPa

Mechanical Characte		eristics	
Item	Test condition	<b>Evaluation standard</b>	
Solderability	Lead terminals are immersed in rosin for 5 seconds and then immersed in the solder bath at +260±5°C for 3±1 seconds	90% min. lead terminals shall be wet with solder. (Except the edge of terminal)	
Soldering Heat Resistance	Lead terminals are immersed in the soldering bath at +260±5°C for 5±0.5 seconds.	No interference in operation.	
Terminal Mechanical Strength	The force 10 seconds of 9.8N is applied to each terminal in axial direction.	No damage and cutting off	
	Lead pads shall be soldered on		

Dimensions	
Pad Layout	Vi

the pc board.

Vibration	The part shall be measured after a vibration of amplitude of 1.5mm with 10Hz to 55Hz band of vibration frequency is applied to each of 3 perpendicular directions for 2 hours.	The value of oscillation frequency/ current consumption should be in ±10% compared with initial ones.
Drop Test	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes(X,Y,Z). A total of 9 times.	The SPL should be in ±10dB compared with initial one.

www.soberton.com



1

## III soberton inc. **PT PIEZO AUDIO TRANSDUCER**

**Acoustic Product Specification** 

#### **Product Number: PT-1109S**



Release | Revision: A/2019

#### CONTENTS

This document contains the technical specifications for the piezo audio transducer.

Page 1 Specifications

Mechanical Characteristics

Page 2 **Environment Test** 

**Reliability Test** 

Page 3 Measuring Method (Speaker Mode)

Soldering Condition

.

Environment Test		
ltem	Test condition	<b>Evaluation standard</b>
High Temp. Test	The part is placed in a chamber at +85°C for 96 hours.	Being placed for 4 hours at +25°C, the buzzer shall be measured. The value of oscillation, frequency / current
Low Temp. Test	The part is placed in a chamber at -40°C for 96 hours.	
Humidity Test	The part is placed in a chamber at +40°C and 90±5% relative humidity for 96 hours.	consumption should be in ±10% compared with initial ones. The SPL should be in ±10dB compared with initial one.
Tonon / Llunaidity /	The next shall be subjected to F	

The part shall be subjected to 5 cycles. Temp/ Humidity One cycle shall consist of:



Reliability Test				
Item	Test condition	Evaluation standard		
Operating Life Test	<ul> <li>1. Continuous Life Test</li> <li>72 hours of continuous</li> <li>operation at +85°C with</li> <li>maximum rated voltage applied</li> <li>2. Intermittent Life Test</li> <li>A duty cycle of 1 minute on,</li> <li>5 minutes off, a minimum of</li> <li>1000 times at +25±2°C</li> <li>and the maximum rated</li> <li>voltage applied</li> </ul>	After the test, the part shall meet specifications without any degradation in appearance and performance except SPL. After 4 hours at +25°C, the SPL should be in ±10dBA compared with initial one.		

#### **Standard Test Condition:**

a) Temperature: +5~+35°C

**b) Humidity:** 45~85%

Page 4 Dimensions	<b>c) Pressure:</b> 86~106KPa	
Pad Layout		
Material Table		
Page 5 Packing		

Cycle

www.soberton.com



2

# 

**Acoustic Product Specification** 

#### Product Number: PT-1109S



#### Release | Revision: A/2019

#### CONTENTS

This document contains the technical specifications for the piezo audio transducer.

#### Page 1

Specifications

Mechanical Characteristics

Page 2 Environment Test

**Reliability Test** 

Page 3 Measuring Method (Speaker Mode)

Soldering Condition

Page 4

#### **Inspection Fixture** S.P.L Measuring Circuit

Input Signal: 5 Vp-p, Square Wave, 4100Hz



MIC: S.P.LmeterTES1351B or equivalent S.G: Hewlett Packard 33120A Function Generator or equivalent

#### **Soldering Condition**

#### Recommended reflow soldering condition is as follows

Reflow soldering is twice

Note: It is requested that reflow soldering should be executed after heat of product goes down to normal temperature



Dimensions	Time [sec]	$\rightarrow$
Pad Layout		
Material Table		
<b>Page 5</b> Packing		
		.lt. i i i

www.soberton.com





**Acoustic Product Specification** 

#### Product Number: PT-1109S



Release | Revision: A/2019

#### CONTENTS

This document contains the technical specifications for the piezo audio transducer.

Page 1 Specifications

Mechanical Characteristics

Page 2 Environment Test

**Reliability Test** 

Page 3 Measuring Method (Speaker Mode)

Soldering Condition

Page 4

Tolerance: ±0.5 (unit: mm)







2

<b>D</b> ·	
L) Impo	ncionc

Pad Layout

Material Table

Page 5 Packing

110.	i al ci tante		Quantity
1	Case	LCP	1
2	Case	LCP	1
3	Piezo	Copper + Ceramics	1
4	Wire	Copper	2

www.soberton.com



4

# will///www.soberton.inc.

## TRANSDUCER

**Acoustic Product Specification** 

#### Product Number: PT-1109S



Release | Revision: A/2019

#### CONTENTS

This document contains the technical specifications for the piezo audio transducer.

Page 1 Specifications

Mechanical Characteristics

Page 2 Environment Test

**Reliability Test** 

Page 3 Measuring Method (Speaker Mode)

Soldering Condition

#### Page 4

#### Packing





<b>D</b> '	•
1)ime	ensions
	11510115

Pad Layout

Material Table

Page 5 Packing

www.soberton.com

