	Wa	TOP N	/IEW	SIDE VII	<b>ΞW</b>					
						15.0 0.8				
	Specifications						Revisio	on History		
	Specifications	Unit		Notes	Version			on History	Date	Approved
Description	Value	Unit			Version 1	Release	Description		<b>Date</b> 10/21/2013	Approved J.S
Description Technology	Value Piezo		1) All dimensions are in mm		Version 1	Release			Date 10/21/2013	Approved J.S
<b>Description</b> Technology Resonant Frequency	Value	(Hz)				Release	Description			
Description Technology Resonant Frequency Rated Voltage	Value       Piezo       2,900		1) All dimensions are in mm			Release	Description			
<b>Description</b> Technology Resonant Frequency	Value       Piezo       2,900       12       95	(Hz) (V)	1) All dimensions are in mm			Release	Description			
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm	Value       Piezo       2,900       12	(Hz) (V)	1) All dimensions are in mm			Release	Description			
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm Tone	Value       Piezo       2,900       12       95       Single	(Hz) (V)	1) All dimensions are in mm			Release	Description			
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm Tone Mount Type	Value   Piezo   2,900   12   95   Single   Thru-hole	(Hz) (V) (dBA)	1) All dimensions are in mm			Release	Description			
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm Tone Mount Type Voltage Range Max Rated Current	Value       Piezo       2,900       12       95       Single       Thru-hole       3 ~ 20       8	(Hz) (V) (dBA) (V) (V)	1) All dimensions are in mm			Release	Description ed from Engi	ineering	10/21/2013	J.S
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm Tone Mount Type Voltage Range	Value       Piezo       2,900       12       95       Single       Thru-hole       3 ~ 20	(Hz) (V) (dBA) (V) (V)	1) All dimensions are in mm				Description			
Description Technology Resonant Frequency Rated Voltage SPL @ 10cm Tone Mount Type Voltage Range Max Rated Current Housing Material	Value       Piezo       2,900       12       95       Single       Thru-hole       3 ~ 20       8       NORYL	(Hz) (V) (dBA) (V) (V) (MA)	1) All dimensions are in mm	unless otherwise noted	1 Drawn by	Date	Description ed from Engi Checked by C.E.	Date	10/21/2013	J.S Date

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.