

**DESCRIPTION**


- With TO-220 package
- Complement to type TIP32/32A/32B/32C

**APPLICATIONS**

- Medium power linear switching applications

**PINNING**

PIN	DESCRIPTION
1	Base
2	Collector; connected to mounting base
3	Emitter


**Absolute maximum ratings(Ta=25 )**

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
V <sub>CBO</sub>	Collector-base voltage	TIP31	40	V
		TIP31A	60	
		TIP31B	80	
		TIP31C	100	
V <sub>CEO</sub>	Collector-emitter voltage	TIP31	40	V
		TIP31A	60	
		TIP31B	80	
		TIP31C	100	
V <sub>EBO</sub>	Emitter-base voltage	Open collector	5	V
I <sub>C</sub>	Collector current (DC)		3	A
I <sub>CM</sub>	Collector current-Pulse		5	A
I <sub>B</sub>	Base current		1	A
P <sub>C</sub>	Collector power dissipation	T <sub>C</sub> =25	40	w
		T <sub>a</sub> =25	2	
T <sub>j</sub>	Junction temperature		150	
T <sub>stg</sub>	Storage temperature		-65~150	

**CHARACTERISTICS**

 T<sub>j</sub>=25 unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT	
V <sub>CEO(SUS)</sub>	Collector-emitter sustaining voltage	TIP31	40			V	
		TIP31A	60				
		TIP31B	80				
		TIP31C	100				
V <sub>CEsat</sub>	Collector-emitter saturation voltage	I <sub>C</sub> =3A I <sub>B</sub> =0.375A			1.2	V	
V <sub>BE</sub>	Base-emitter on voltage	I <sub>C</sub> =3A ; V <sub>CE</sub> =4V			1.8	V	
I <sub>CES</sub>	Collector cut-off current	TIP31	V <sub>CE</sub> =40V; V <sub>EB</sub> =0			0.2	mA
		TIP31A	V <sub>CE</sub> =60V; V <sub>EB</sub> =0				
		TIP31B	V <sub>CE</sub> =80V; V <sub>EB</sub> =0				
		TIP31C	V <sub>CE</sub> =100V; V <sub>EB</sub> =0				
I <sub>CEO</sub>	Collector cut-off current	TIP31/31A	V <sub>CE</sub> =30V; I <sub>B</sub> =0			0.3	mA
		TIP31B/31C	V <sub>CE</sub> =60V; I <sub>B</sub> =0				
I <sub>EBO</sub>	Emitter cut-off current	V <sub>EB</sub> =5V; I <sub>C</sub> =0			1.0	mA	
h <sub>FE-1</sub>	DC current gain	I <sub>C</sub> =1A ; V <sub>CE</sub> =4V	25				
h <sub>FE-2</sub>	DC current gain	I <sub>C</sub> =3A ; V <sub>CE</sub> =4V	10		50		
f <sub>T</sub>	Transiton frequency	I <sub>C</sub> =0.5A ; V <sub>CE</sub> =10V	3			MHz	

PACKAGE OUTLINE




Fig.2 Outline dimensions (unindicated tolerance:  $\pm 0.10$  mm)




Fig.3 DC current Gain




Fig.4 Base-Emitter Saturation Voltage  
Collector-Emitter Saturation Voltage




Fig.5 Safe Operating Area