

East Electronics



Product Specification

48273 Lakeview Blvd Fremont, CA 94538, U.S.A Tel: 510-413-0002 Fax: 510-413-0010

http://www.east-elec.com

Product Name:	Piezo Buzzer
Part Number:	EFM-620LA
Version:	1.02
Date:	2017/10/10
Note:	

Company passed ISO 9001 / ISO TS16949 / ISO 14001 Certifications


Revision History

Rev.	Description	Author/Date	Checked By	Approver
1.02	Change the company name to East Electronics	SYSTEM 2017-10-10		
1.01	Quality Certificate Symbol revised	吕文斌 2015-2-9	汤礼东	王建成
1.0	Released	汤礼东 2011-12-21	张春雷	王建成

East Electronics 1/5

1. Part Number EFM-620LA

2. Dimension Drawing (Unit: mm)



3. Specification


No.	Item	Specification
3-1	Min. Sound Pressure Level	90dB/9V _{DC} /100cm
	*Min. Sound Pressure Level	100dB/9V _{DC} /100cm
3-2	Rated Voltage	9V _{DC}
3-3	Max. Consumption	50mA/9V _{DC}
3-4	Oscillating Frequency	2.8±0.5 kHz
3-5	Tone Nature	Continuous
3-6	Operating Temperature	-20~+60°C
3-7	Case Material/Color	ABS/Black
3-8	Weight	12.5g
3-9	Wire Standard	UL1095-22AWG

NOTES:

- 1, *The sound pressure could reach 100dB(A) if our buzzer were put into your housing.
- 2. Test should be made under the conditions of room temperature $(20\pm10^{\circ}\text{C})$, normal humidity $(60\pm20\%)$ and normal atmospheric pressure. In this case, however, that the judgment is questionable, the test conditions are to be changed to room temperature $20\pm2^{\circ}\text{C}$, relative humidity $60\sim70\%$ and normal atmospheric pressure

East Electronics 2/5

4.Typical Frequency Response Curve




Note:Distance 100 cm

East Electronics 3/5

5. Reliability Test


No.	Item	Method of Test	Tolerance after Testing	
5-1	Operating Temperature	-20~+60°C	Sound pressure level initial value ±10dB Max. consumption value ±20% Oscillating Frequency value ±20%	
5-2	Storage in high temperature	Storage in +60°C test box 96 hours then exposed to the room temperature for 2 hours		
5-3	Storage in low temperature	Storage in -20°C test box 96 hours then exposed to the room temperature for 2 hours		
5-4	Life test in the room temperature	Operate the product continuously 5 seconds on 5 seconds off 300 hours at rated voltage		
5-5	Temperature / humidity cycle test	Storage in +40°C, 93±3%RH test box 96 hours then exposed to the room temperature for 2 hours		
5-6	Temperature (high and low) cycle test	Conduct the test for 5 cycles without applying power then expose to the room temperature for 2 hours.(See Figure 5-6)		
5-7	Vibration test	Conduct the test for the directions of X Y and Z for 0.5 hour each (total 1.5 hours). To-and Fri sweep time(from 10 to 55Hz and then 55 to 10) under single amplitude of 0.75mm is 3 minute, then expose to the room temperature for 2 hours		
5-8	Drop test	Drop a product naturally from the height of 700mm onto the surface of 100mm thick wooden board. Two directions: upper and side of the product are to be applied for this drop test once respectively		

Figure 5-6



East Electronics 4/5

6. Electrical Testing Method



S.P.L.M	Sound Pressure Level Meter
T.S	Testing Sample
F.C	Frequency Counter
P.S	Power Supply
D.V.M	DC Voltage Meter
D.A.M	DC Ampere Meter

7. Packing Information

Packing: 800 pcs per export carton Carton Size: $47 \times 30.5 \times 29$ cm

G. Weight: 12.8 kgs N. Weight: 10.0 kgs

East Electronics 5/5