

SPECIFICATIONS				
PARAMETERS	VALUES	UNIT		
RATED VOLTAGE	3	Vpk		
OPERATING VOLTAGE RANGE	2 ~ 4	Vpk		
RATED CURRENT (MAX)	70	mA		
COIL RESISTANCE	15 ± 3	ОНМ		
MINIMUM SPL @ 10 CM	90	dBA		
RESONANT FREQUENCY	2,730 ± 500	Hz		
OPERATING TEMPERATURE	-20 ~ +70	°C		
STORAGE TEMPERATURE	-30 ~ +80	°C		
HOUSING MATERIAL	NORYL	-		
TERMINAL MATERIAL	Au PLATED BRASS	-		
WEIGHT	1	grams		


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PUI AUDIO, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PUI AUDIO, INC. IS PROHIBITED.


©2010, PUI AUDIO Inc.

REVISION HISTORY				
LTR	DESCRIPTION	DATE	APPROVED	
-	RELEASED FROM ENGINEERING	08/07/2014		
Α	CORRECTED PART WEIGHT	10/27/2016	M.L.	
В	B UPDATED HOUSING DIMENSIONS 7/28/2017 M.V.			
С	REVISED MAX CURRENT	2/14/2020	M.L.	









Date

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2015/863/EU COMPLIANT.

UNLESS OTHERWISE SPECIFIED:	Γ
All PURCHASES ARE SUBJECT TO AND	ı
INCORPORATE THE PUI AUDIO TERMS	ı
AND CONDITIONS SALE FOUND AT	ı
http://www.puiaudio.com	ı
/pdf/terms_conditions.pdf	ı
(paper copy available upon request).	ı
DIMENSIONS ARE IN MILLIMETERS,	ı
TOLERANCES ARE ±0.5 AND	ı
ANGLES ARE +3°	ı

SIZE

A3

	pul audio n
\bigvee	a projects unlimited company

Date

8/7/2014

Checked by

Designed by

J.D.

C.W. 8/7/2014 B.R. 8/7/2014 8/7/2014

Date

Drawn Date

1 / 1

Approved by

AT-1127-ST-2-R RevB

Transducer (Electro-Mech)

4

AT-1127-ST-2-R RevB.idw