

PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4216-2



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the Piezo Audio Buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Inspection Fixture

Frequency Response

Page 4

Dimensions

Page 5

Packing

Specifications					
Item	Unit	Specification	Condition		
Rated Voltage	VDC	12.0	<u></u>		
Operating Voltage	VDC	3.0 ~ 20.0	0V		
Mean Current	mA	10.0 Max.	At rated voltage		
Sound Output	dB	90	At 30cm at rated voltage.		
Rated Frequency	Hz	2800±500			
Operating Temp	°C	-20 ~ +55			
Storage Temp	°C	-30 ~ +70			
Dimension	mm	Ø41.6xH16.0	See attached drawing.		
Weight	gram	9.0			
Material		ABS(Black)			
Terminal		Wire Type	Wire 140mm (UL1007/AWG26#)		
Environmental Protection Regulation		RoHS			

Test condition:

Temperature: +25±2°C **Related Humidity:** 65±5% **Air Pressure:** 86-106KPa

	Mechanical Characteristics		
Item	Test Condition	Evaluation Standard	
Solderability	Lead terminals are immersed in rosin for 5 seconds and then immersed in the solder bath at +250±5°C for 3±1 seconds.	90% min. lead terminals shall be wet with solder. (Except the edge of terminal)	
Soldering Heat Resistance	Lead terminals are immersed in the soldering bath at +250±5°C for 3±1seconds. The force of 9.8N(1.0Kg) is applied to the part for 10 seconds.	No interference in operation.	
Terminal Mechanical Strength	The pull force shall be applied to double lead wires: Horizontal 3.0N(0.306kg) for 30 seconds. Vertical 2.0N(0.204kg) for 30 seconds.	No damage and cutting off.	
Vibration	The buzzer shall be measured after a vibration of amplitude of 1.5mm with 10Hz to 55Hz band of vibration frequency is applied to each of 3 perpendicular directions for 2 hours	The value of oscillation frequency current consumption should be in±10% compared with initial ones. The SPL should be in±10dB compared with initial one.	
Drop Test	The part is dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X,Y,Z). A total of 9 times.		



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4216-2



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the Piezo Audio Buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Inspection Fixture

Frequency Response

Page 4

Dimensions

Page 5

Packing

Environment Test				
Item	Test Condition	Evaluation Standard		
High Temp. Test	The part is placed in a chamber at +70°C for 96 hours.	After the test, the part shall meet specifications without any		
Low Temp. Test	The part is placed in a chamber at -30°C for 96 hours.	degradation in appearance and		
Humidity Test	The part is placed in a chamber at +70°C, and 90±5% relative humidity for 96 hours.	performance except SPL. After 4 hours at +25°C ±2°C, the SPL should be in ±10dBA compared with initial one.		
Temp/Humidity Cycle	The part shall be subjected to 5 c	ycles,		

	+2	25°C	/	+70°	c \	+25
0.5hr	0.5hr	0.25	0.5 h r	0.5hr	0.5h	0.25
←	\longleftrightarrow	+	←→ 3h	d → ours	\longleftrightarrow	*

Reliability Test				
Item	Test Condition	Evaluation Standard		
Operating Life Test	 Continuous Life Test 48 hours of continuous operation at +55°C with the maximum rated voltage applied. Intermittent Life Test A duty cycle of 1 minute on, 1 minute off, a minimum of 1000 times at +25±2°C and the maximum rated voltage applied. 	After the test, the part shall meet specifications without any degradation in appearance and performance except SPL. After 4 hours at +25°C ±2°C, the SPL should be in ±10dBA compared with initial one.		

Standard Test Condition:

a) Temperature: +5~+35°C

b) Humidity: 45~85%

c) Pressure: 86~106KPa



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4216-2



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the Piezo Audio Buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Inspection Fixture

Frequency Response

Page 4

Dimensions


Page 5

Packing


Inspection Fixture


S.P.L Measuring Circuit

Input Signal: 12 VDC MIC: S.P.L meter TES1351B or equivalent



Frequency Response







PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4216-2



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the Piezo Audio Buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Inspection Fixture

Frequency Response

Page 4


Dimensions


Page 5


Packing

Dimensions

Tolerance: ±0.5 (unit: mm)







No.	Part Name	Material	Quantity
1	Case	ABS	1
2	Cover	ABS	1
3	Piezo	Brass + Ceramic	1
4	Wire (140mm)	UL1007 AWG26# (300V/ 1.3mm)	2
5	Wire	Copper	3
6	PCB	Ероху	1



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4216-2



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the Piezo Audio Buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Inspection Fixture

Frequency Response


Page 4

Dimensions

Page 5

Packing

Packing



Packing Box	L x W x H (mm)	Quantity (pcs)
Per Box	300 x 200 x 50	72
Per Carton (12 Boxes)	430 x 320 x 280	864