


此处禁部机购



RECOMMEND PCB LAYOUT: ■ PCB AREA 焊接区
(Unit:mm .X ± 0.15 .XX ± 0.05 .XXX ± 0.02)


PIN NO.	PIN ASSIGNMENT
1#	DAT2 信号
2#	CD/DAT3 信号
3#	CMD 数据输入
4#	VDD 电压/电
5#	CLK 时钟
6#	VSS 接地
7#	DATO 信号
8#	DAT1 信号
CD	侦测P
P9	VDD2 SUPPLY VOLTAGE(L.SV)
P10	VSS SUPPLY VOLTAGE GROUND
P11	D0+ UHS-I1 D0+
P12	D0- UHS-I1 D0-
P13	VSS SUPPLY VOLTAGE GROUND
P14	D1- UHS-I1 D1-
P15	D1+ UHS-I1 D1+
P16	VSS SUPPLY VOLTAGE GROUND
P17	SWIO Single Wire Protocol Interface

Specification

MATERIAL:
 Insulator: High Temperature Thermoplastic,
 UL 94V-0, COLOR"BLACK LCP
 (塑胶: 黑色LCP, 防火等级UL 94V-0)
 SHELL: SUS301
 Contact: Copper Alloy (磷铜C5210)
 弹簧: 琴钢丝
 拉杆: SUS301

PLATING:
 Contact: All Ni50u, contact area 1u Au, Pad 0.8u Au
 (接触端子电镀: 全部镀底50U, 接触区域1u金, 焊脚处0.8u金最小)
 Shell: All 50u Ni, Pad 0.8 Au
 (外壳电镀: 镀底50U, 焊接处0.8u金)

Electrical:
 Current Rating :0.5amps max(额定电流:0.5A最大)
 Voltage Rating :5V AC/DC(额定电压:5V AC/DC)
 Ambient Temperature Range :-20° C+60° C(工作温度:-20度到+60度)
 Storage Temperature Range :-40° C+70° C(工作环境:-20度到+80度)
 Ambient Humidity Range :95% R.H. Max. (上锡效果: 95%以上)
 Contact Resistance:100Ωmax. (端子接触电阻: 100Ω最大)
 Insulation Resistance:1000Ωmin./500VDC(绝缘阻抗: 100兆欧最小)
 Mating Cycles:3,000 Insertions (寿命: 3000次)
 产品耐温温度: 260° C



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: TF PUSH 4.0卡座 1.5H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW126-TF18-150B
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2106041020
SCALE:1:1	SIZE: A4		SHEET NO. 1 OF 1