



SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer Nylon66 UL94-VO(2)  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-PH-2AW-B	2.00	6.00
3	XD-PH-3AW-B	4.00	8.00
4	XD-PH-4AW-B	6.00	10.00
5	XD-PH-5AW-B	8.00	12.00
6	XD-PH-6AW-B	10.00	14.00
7	XD-PH-7AW-B	12.00	16.00
8	XD-PH-8AW-B	14.00	18.00
9	XD-PH-9AW-B	16.00	20.00
10	XD-PH-10AW-B	18.00	22.00
11	XD-PH-11AW-B	20.00	24.00
12	XD-PH-12AW-B	22.00	26.00
13	XD-PH-13AW-B	24.00	28.00
14	XD-PH-14AW-B	26.00	30.00
15	XD-PH-15AW-B	28.00	32.00
16	XD-PH-16AW-B	30.00	34.00

Ordering Information

XD - PH - N \*\*\* - \* - \*\*



			GENERAL TOLERANCE	制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-PH-NAW-B	单位 UNITS	mm
			X.XX ±0.20	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						