

# HR911130C

#### Electrical Specification @25°C

RoHS Compliant (PB Free)

Operating Temperature Range: 0°C ~ +70°C

Isolation: 2250Vdc 0.5mA 60sec (UTP Side to Chip Side)

OCL: 350uH Minimum @100KHz 100mV with 8mADC Insertion Loss: -1.0dB Maximum @100KHz ~ 60MHz -1.1dB Maximum @60MHz ~ 100MHz

Return Loss: -18dB Minimum @0.3MHz ~ 30MHz / -14dB Minimum @40MHz ~ 60MHz

−12dB Minimum @80MHz ~ 100MHz


Common Mode Rejection:  $-40 \, \text{dB}$  Minimum @1MHz  $\sim 60 \, \text{MHz}$ 

-35dB Minimum @60MHz  $\sim 100$ MHz

Crosstalk: -35dB Minimum @1MHz  $\sim$  10MHz / -26dB Minimum @15MHz  $\sim$  60MHz

−24dB Minimum @60MHz ~ 100MHz

#### **Schematics**



REV.: B 1 of 4





# HR911130C


- RoHS Compliant (PB Free)
- Meets or Exceeds IEEE802.3ab standards including 350uH Min OCL with 8mADC
- High performance for EMI suppression, Crosstalk, Return Loss and Consistent Electrical
- Minimum 2250Vdc isolation per IEEE802.3 requirement
- Minimize PCB space and Simplify PCB Layout
- Less magnetic components to be placed on PCB, higher reliability and yields
- UL Recognized Component: File # E330599

#### Mechanical Dimensions:









Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Туре
Green	568nm	1.8V/2.8V	20mA	squareness
Yellow	585nm	1.8V/2.8V	20mA	squareness

Dimensions in mm


Unless otherwise specified, Tolerance: .xx  $\pm 0.25$ 

REV.: B 2 of 4




# HR911130C

# PCB Layout:



Recommended PCB layout (Component Side View) All dimension tolerance are  $\pm 0.08$  unless otherwise specified

# Suggested Panel Cutout:



SUGGESTED PANEL OPENING

Dimensions in mm

Unless otherwise specified, Tolerance: .xx  $\pm 0.25$ 

REV.: B 3 of 4

# Single Port RJ45 Connector with Integrated Magnetics and LED



# HR911130C

# Material Specification:

Housing: PA66 GF Black UL94V-0

Shield: 30u" Nickel over 0.20mm Thickness Brass

Insert: PA66 GF Black UL94V-0

Phosphor Bronze 0.35mm Thickness Plating Area, 30u" gold over 50u" nickel Solder Area, 100u" tin over 50u" nickel

#### Mechanical Performance:

Mating force: 5 lbs Maximum Unmating force: 5 lbs Maximum

Plug to Jack Retention force: 12 lbs Minimum

Operating life: 750 Cycles Minimum

# Operating and Storage Temperature:

Operating Temperature Range:  $0^{\circ}\text{C} \sim +70^{\circ}\text{C}$ Storage Temperature Range:  $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 

REV.: B 4 of 4