





- NOTE:
1. Rating: 24V 25mA DC
 2. Contact Resistance: 50mΩ max
 3. Dielectric Strength: 500V AC/1Minute
 4. Operating Force: 1000gf Max
 5. Operating Life: 2,000 Cycles



Position(位数)	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
DIM.A(长径)	6.64	9.18	11.72	14.26	16.80	19.34	21.88	24.42	26.96	32.04
DIM.B(长径)	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94

PART NO.	凸柄 (P)	短柄 (S)	凸柄 (R)	凸柄 (P)	短柄 (S)
DA-02RP	DA-03RP	DA-04RP	DA-05RP	DA-06RP	DA-07RP
DA-02RS	DA-03RS	DA-04RS	DA-05RS	DA-06RS	DA-07RS
DA-02BP	DA-03BP	DA-04BP	DA-05BP	DA-06BP	DA-07BP
DA-02BS	DA-03BS	DA-04BS	DA-05BS	DA-06BS	DA-07BS

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/6/26
CHECKED		
APPROVALS		

TOLERANCES ARE

30 ^{±0.15}	±0.30	ANGLE
10 ^{±0.10}	±0.20	
5 ^{±0.10}	±0.15	

ITEM PART NAME QTY. MATERIAL FINISHING

⑤	Gum Water	X	Epikote	Black
④	Terminal	X	Phosphor bronze	Au Plating
③	Base	1	PBT	Black
②	Cover	1	PBT	Red/Blue
①	Keystoke	1	PBT	White

APPROVALS DATE

DIP SWITCHES

DA-XXXX

ELECTRONICS CO.,LTD

