



PCB LAYOUT

3	焊片 Fitting Nail	黄铜 Brass	2	镀锡 Tin-plated
2	端子 Terminal	黄铜 Brass	N	镀锡 Tin-plated
1	底座 Housing	LCP UL94-V0	1	本色 Natural color
序号 No.	名称 Part Name	材料 Material	数量 Qty	备注 Remark

技术要求Notes:  
 1.外观质量 Appearance quality:  
 a.金属表面镀层不能有明显损伤;  
 Coating on metal surface can not be damaged obviously;  
 b.塑壳表面不能有明显的变形或开裂;  
 No obvious deformation or cracking can be observed on the surface of the Housing;  
 c.产品表面应保持清洁;  
 Product surface should be kept clean;  
 2.工作温度 Working temperature: -25℃~+85℃;  
 3.额定电压 Voltage Rating : Max 125V [AC/Effective value mvs]/DCI;  
 4.额定电流 Current Rating: Max 1A [AC/Effective value mvs]/DCI;  
 5.接触电阻 Contact resistance: Max 20 mΩ;  
 6.绝缘电阻 Insulation resistance: Min 100MΩ;  
 7.耐压 Withstanding voltage: 500V AC(50 Hz. Effective value: 1 min);  
 8.环保要求应符合RoHS标准  
 Environmental requirements should meet RoHS standards.

16	1.25-16PS	18.75	24.80	17.50
15	1.25-15PS	17.50	23.55	16.25
14	1.25-14PS	16.25	22.30	15.00
13	1.25-13PS	15.00	21.05	13.75
12	1.25-12PS	13.75	19.80	12.50
11	1.25-11PS	12.50	18.55	11.25
10	1.25-10PS	11.25	17.30	10.00
9	1.25-9PS	10.00	16.05	8.75
8	1.25-8PS	8.75	14.80	7.50
7	1.25-7PS	7.50	13.25	6.25
6	1.25-6PS	6.25	12.30	5.00
5	1.25-5PS	5.00	11.05	3.75
4	1.25-4PS	3.75	9.80	2.50
3	1.25-3PS	2.50	8.55	-
2	1.25-2PS	1.25	7.30	-
孔位	产品型号	DIM A	DIM B	DIM C
CKT NO.	PART TYPE			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS	DATE	DEALON 德之隆® ELECTRONICS CO.,LTD	
DRAWN	2022/7/17	TITLE:	1.25mm Crimp Style Connectors
CHECKED		PART NO.	1.25-□□□□
APPROVALS		UNIT: mm	SCALE: 1:1
TOLERANCES ARE		DRAWING NO.	SHEET 1 OF 1
30±0.15	±0.30	ANGLE	PROJ
10±0.10	±0.20		
5±0.05	±0.15	±2°	
~5	±0.10		