# N-Channel 60-V (D-S) MOSFET


FEATURES
----------

GO

- 175 °C Junction Temperature
- TrenchFET<sup>®</sup> Power  $\dot{MOSFET}$

D

• Material categorization:



S N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS (T <sub>C</sub> = 25	°C, unless otherw	vise noted)		
Parameter	Symbol	Limit	Unit	
Gate-Source Voltage		V <sub>GS</sub>	± 20	V
$O_{\rm entire optime} O_{\rm entire optime} (T_{\rm entire optime} = 475 ^{\circ}O_{\rm e})$	T <sub>C</sub> = 25 °C	1-	70	
Continuous Drain Current (T <sub>J</sub> = 175 °C)⁵	T <sub>C</sub> = 100 °C		50ª	
Pulsed Drain Current	I <sub>DM</sub>	200	A	
Continuous Source Current (Diode Conduction)	I <sub>S</sub>	50ª		
Avalanche Current		I <sub>AS</sub>	50	
Single Avalanche Energy (Duty Cycle $\leq$ 1 %)	L = 0.1 mH	E <sub>AS</sub>	125	mJ
Movimum Power Dissinction	T <sub>C</sub> = 25 °C	Pn –	136	w
Maximum Power Dissipation	T <sub>A</sub> = 25 °C		3 <sup>b</sup> , 8.3 <sup>b, c</sup>	V
Operating Junction and Storage Temperature Range	·	T <sub>J</sub> , T <sub>stg</sub>	- 55 to 175	°C

THERMAL RESISTANCE RATINGS						
Parameter		Symbol	Typical	Maximum	Unit	
Maximum Junction-to-Ambient <sup>a</sup>	t ≤ 10 sec	R <sub>thJA</sub>	15	18		
	Steady State		40	50	°C/W	
Maximum Junction-to-Case		R <sub>thJC</sub>	0.85	1.1		

Notes:

a. Package limited.

b. Surface mounted on 1" x 1" FR4 board.

c.  $t \leq$  10 s.

PRODUCT SUMMARY					
V <sub>DS</sub> (V)	<b>R<sub>DS(on)</sub> (</b> Ω <b>)</b>	I <sub>D</sub> (A) <sup>a</sup>			
60	0.010 at V <sub>GS</sub> = 10 V	70			
00	0.012 at V <sub>GS</sub> = 4.5 V	55			





Parameter	Symbol	Test Conditions	Min.	Typ.ª	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	akdown Voltage $V_{DS}$ $V_{GS}$ = 0 V, $I_D$ = 250 $\mu$ A 60		60			V	
Gate Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$	1	2	3	V	
Gate-Body Leakage	I <sub>GSS</sub>	$V_{DS} = 0 V, V_{GS} = \pm 20 V$			± 100	nA	
		$V_{DS} = 60 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	1		1		
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS}$ = 60 V, $V_{GS}$ = 0 V, $T_{J}$ = 125 °C			50	μΑ	
		$V_{DS}$ = 60 V, $V_{GS}$ = 0 V, $T_{J}$ = 175 °C			250		
On-State Drain Current <sup>b</sup>	I <sub>D(on)</sub>	V <sub>DS</sub> = 5 V, V <sub>GS</sub> = 10 V	60			А	
		V <sub>GS</sub> = 10 V, I <sub>D</sub> = 20 A		0.010			
		$V_{GS}$ = 10 V, I <sub>D</sub> = 20 A, T <sub>J</sub> = 125 °C		0.016		Ω	
Drain-Source On-State Resistance <sup>b</sup>	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 20 A, T <sub>J</sub> = 175 °C		0.020			
		V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 15 A		0.012			
Forward Transconductance <sup>b</sup>	9 <sub>fs</sub>	V <sub>DS</sub> = 15 V, I <sub>D</sub> = 20 A		60		S	
Dynamic							
Input Capacitance	C <sub>iss</sub>			2650			
Output Capacitance	C <sub>oss</sub>	$V_{GS}$ = 0 V, $V_{DS}$ = 25 V, f = 1 MHz		470		pF	
Reverse Transfer Capacitance	C <sub>rss</sub>			225			
Total Gate Charge <sup>c</sup>	Qg			47	70		
Gate-Source Charge <sup>c</sup>	Q <sub>gs</sub>	$V_{DS}$ = 30 V, $V_{GS}$ = 10 V, $I_D$ = 50 A		10		nC	
Gate-Drain Charge <sup>c</sup>	Q <sub>gd</sub>			12			
Turn-On Delay Time <sup>c</sup>	t <sub>d(on)</sub>			10	20		
Rise Time <sup>c</sup>	t <sub>r</sub>	$V_{DD}$ = 30 V, R <sub>L</sub> = 0.6 Ω I <sub>D</sub> ≅ 50 A, V <sub>GEN</sub> = 10 V, R <sub>g</sub> = 2.5 Ω		15	25	ns	
Turn-Off Delay Time <sup>c</sup>	t <sub>d(off)</sub>			35	50		
Fall Time <sup>c</sup>	t <sub>f</sub>			20	30		
Source-Drain Diode Ratings and Cha	aracteristics (	T <sub>C</sub> = 25 °C)			I		
Pulsed Current	I <sub>SM</sub>				70	А	
Diode Forward Voltage	V <sub>SD</sub>	I <sub>F</sub> = 20 A, V <sub>GS</sub> = 0 V		1	1.5	V	
Reverse Recovery Time	t <sub>rr</sub>	I <sub>F</sub> = 20 A, di/dt = 100 A/μs		45	100	ns	

Notes:

a. For design aid only; not subject to production testing.

b. Pulse test; pulse width  $\leq$  300 µs, duty cycle  $\leq$  2 %.


c. Independent of operating temperature.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

VBsemi /Bsemi.com




### TYPICAL CHARACTERISTICS (25 °C unless noted)








## TYPICAL CHARACTERISTICS (25 °C unless noted)



(Y) Hend (Y) He




#### THERMAL RATINGS



Normalized Thermal Transient Impedance, Junction-to-Case



## **TO-220 FULLPAK (HIGH VOLTAGE)**



	MILLIMETERS		INC	CHES	
DIM.	MIN.	MAX.	MIN.	MAX.	
A	4.570	4.830	0.180	0.190	
A1	2.570	2.830	0.101	0.111	
A2	2.510	2.850	0.099	0.112	
b	0.622	0.890	0.024	0.035	
b2	1.229	1.400	0.048	0.055	
b3	1.229	1.400	0.048	0.055	
С	0.440	0.629	0.017	0.025	
D	8.650	9.800	0.341	0.386	
d1	15.88	16.120	0.622	0.635	
d3	12.300	12.920	0.484	0.509	
E	10.360	10.630	0.408	0.419	
е	2.5	4 BSC	0.100	BSC	
L	13.200	13.730	0.520	0.541	
L1	3.100	3.500	0.122	0.138	
n	6.050	6.150	0.238	0.242	
ØP	3.050	3.450	0.120	0.136	
u	2.400	2.500	0.094	0.098	
V	0.400	0.500	0.016	0.020	
ECN: X09-0126-Rev. B, 20 DWG: 5972	6-Oct-09				

#### Notes

1. To be used only for process drawing. 2. These dimensions apply to all TO-220, FULLPAK leadframe versions 3 leads. 3. All critical dimensions should C meet  $C_{pk} > 1.33$ . 4. All dimensions include burrs and plating thickness. 5. No chipping or package damage.



# Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

# **Material Category Policy**

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.