

N-Channel 80 V (D-S) MOSFET

PRODUCT SUMMARY		
V _{DS}	80	V
$R_{DS(on)} V_{GS} = 10 V$	7	mΩ
$R_{DS(on)}$ $V_{GS} = 4.5 \text{ V}$	9	mΩ
I _D	100	Α
Configuration	Single	


FEATURES

- TrenchFET® Power MOSFET
- \bullet 100 % R_g and UIS Tested




APPLICATIONS

- Primary Side Switching
- Synchronous Rectification
- DC/AC Inverters
- LED Backlighting



N-Channel MOSFET

то	-22	0AE



ABSOLUTE MAXIMUM RATINGS	T _A = 25 °C, unless	otherwise not	ed)		
Parameter		Symbol	Limit	Unit	
Drain-Source Voltage		V _{DS}	80	V	
Gate-Source Voltage		V _{GS}	± 20	V	
	T _C = 25 °C		100ª		
Continuous Dunin Comment (T. 150 °C)	T _C = 70 °C	1 . [85 ^a		
Continuous Drain Current (T _J = 150 °C)	T _A = 25 °C	l _D	28.6 ^{b, c}		
	T _A = 70 °C	- 	24.9 ^{b, c}	^	
Pulsed Drain Current (t = 100 μs)	-	I _{DM}	350	Α	
Continuous Source-Drain Diode Current	T _C = 25 °C	I _S	80 ^a		
	T _A = 25 °C		4.5 ^{b, c}		
Single Pulse Avalanche Current	Ilse Avalanche Current		30		
Single Pulse Avalanche Energy	L = 0.1 mH	E _{AS}	45	mJ	
Maximum Power Dissipation	T _C = 25 °C		180		
	T _C = 70 °C		120	147	
	T _A = 25 °C	P _D	5 ^{b, c}	W	
	T _A = 70 °C		3.2 ^{b, c}		
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150	00	
Soldering Recommendations (Peak Temperatur		260	°C		

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^a	t ≤ 10 sec	R_{thJA}	15	18	
	Steady State		40	50	°C/W
Maximum Junction-to-Case		R_{thJC}	0.85	1.1	

Notes

- a. Package limited.
- b. Surface mounted on 1" x 1" FR4 board.
- c. t = 10 s.

服务热线:400-655-8788

1




Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit
Static						
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	80			V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$			37		1400
V _{GS(th)} Temperature Coefficient	$\Delta V_{GS(th)}/T_J$	I _D = 250 μA		- 6.1		mV/°C
Gate-Source Threshold Voltage	V _{GS(th})	$V_{DS} = V_{GS}, I_D = 250 \mu A$	2.0		3.5	V
Gate-Source Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA
Zaura Onto Valta na Duniu Ocumant	_	$V_{DS} = 80 \text{ V}, V_{GS} = 0 \text{ V}$			1	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 80 V, V _{GS} = 0 V, T _J = 55 °C			10	μA
On-State Drain Currenta	I _{D(on)}	$V_{DS} \ge 5 \text{ V}, V_{GS} = 10 \text{ V}$	85			Α
		$V_{GS} = 10 \text{ V}, I_D = 20 \text{ A}$		7		
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = 6 V, I _D = 15 A		7. 5		mΩ
	, ,	$V_{GS} = 4.5 \text{ V}, I_D = 10 \text{ A}$		9		1
Forward Transconductance ^a	9 _{fs}	$V_{DS} = 10 \text{ V}, I_D = 20 \text{ A}$		60		S
Dynamic ^b						
Input Capacitance	C _{iss}			3855		
Output Capacitance	C _{oss}	$V_{DS} = 40 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		1120		pF
Reverse Transfer Capacitance	C _{rss}			376		
	Qg	$V_{DS} = 40 \text{ V}, V_{GS} = 10 \text{ V}, I_D = 10 \text{ A}$		35.5		nC
Total Gate Charge		$V_{DS} = 40 \text{ V}, V_{GS} = 6 \text{ V}, I_D = 10 \text{ A}$		22		
				18		
Gate-Source Charge	Q_{gs}	$V_{DS} = 40 \text{ V}, V_{GS} = 4.5 \text{ V}, I_D = 10 \text{ A}$		5.3		IIC
Gate-Drain Charge	Q_{gd}			7.3		
Output Charge	Q _{oss}	$V_{DS} = 40 \text{ V}, V_{GS} = 0 \text{ V}$		57	86	
Gate Resistance	R_g	f = 1 MHz	0.5	1.3	2	Ω
Turn-On Delay Time	t _{d(on)}			12	24	
Rise Time	t _r	$V_{DD} = 40 \text{ V}, R_L = 4 \Omega$		8	16	
Turn-Off DelayTime	t _{d(off)}	$I_D \cong 10 \text{ A}, V_{GEN} = 10 \text{ V}, R_g = 1 \Omega$		32	64	
Fall Time	t _f			7	14	no
Turn-On Delay Time	t _{d(on)}			14	28	ns
Rise Time	t _r	$V_{DD} = 40 \text{ V}, R_L = 4 \Omega$		11	22	
Turn-Off DelayTime	t _{d(off)}	$I_D\cong\ 10\ A,\ V_{GEN}=6.0\ V,\ R_g=1\ \Omega$		30	60	
Fall Time	t _f			8	16	
Drain-Source Body Diode Characteristic	s					
Continuous Source-Drain Diode Current	I _S	T _C = 25 °C			75	A
Pulse Diode Forward Current (t = 100 μ s)	I _{SM}				150	
Body Diode Voltage	V_{SD}	I _S = 5 A		0.76	1.1	V
Body Diode Reverse Recovery Time	t _{rr}			38	75	ns
Body Diode Reverse Recovery Charge	Q _{rr}	I _F = 10 A, dl/dt = 100 A/µs, T _J = 25 °C		36	70	nC
Reverse Recovery Fall Time	ta	$I_{F} = 10 \text{ A}, \text{ al/at} = 100 \text{ A/}\mu\text{s}, I_{J} = 25 \text{ C}$		19		ne
Reverse Recovery Rise Time	t _b			19		ns


Notes

- a. Pulse test; pulse width $\leq 300~\mu s,~duty~cycle \leq 2~\%.$
- b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.










120






Capacitance









On-Resistance vs. Junction Temperature







Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power, Junction-to-Ambient





Safe Operating Area, Junction-to-Ambient






Current Derating*









Power, Junction-to-Ambient

^{*} The power dissipation P_D is based on $T_{J(max.)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.






Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case



TO-220AB



	MILLIMETERS		INC	HES	
DIM.	MIN.	MAX.	MIN.	MAX.	
Α	4.25	4.65	0.167	0.183	
b	0.69	1.01	0.027	0.040	
b(1)	1.20	1.73	0.047	0.068	
С	0.36	0.61	0.014	0.024	
D	14.85	15.49	0.585	0.610	
E	10.04	10.51	0.395	0.414	
е	2.41	2.67	0.095	0.105	
e(1)	4.88	5.28	0.192	0.208	
F	1.14	1.40	0.045	0.055	
H(1)	6.09	6.48	0.240	0.255	
J(1)	2.41	2.92	0.095	0.115	
L	13.35	14.02	0.526	0.552	
L(1)	3.32	3.82	0.131	0.150	
ØΡ	3.54	3.94	0.139	0.155	
Q	2.60	3.00	0.102	0.118	
ECN: X12-0208-Rev. N, 08-Oct-12					

DWG: 5471 Notes

 $^{^{\}star}$ M = 1.32 mm to 1.62 mm (dimension including protrusion) Heatsink hole for HVM



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.