

**Surface Mount General Purpose Silicon Rectifiers**
**Reverse Voltage - 50 to 1000 V**
**Forward Current - 1 A**
**FEATURES**

- ◆ For surface mounted applications
- ◆ Low profile package
- ◆ Glass Passivated Chip Junction
- ◆ Ideal for automated placement
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives


**MECHANICAL DATA**

- ◆ Case: SOD-123FL
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 15mg / 0.00053oz

**Maximum Ratings and Electrical characteristics**

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.




Marking Code	
<b>DSR1A</b>	<b>A1</b>
<b>DSR1B</b>	<b>A2</b>
<b>DSR1D</b>	<b>A3</b>
<b>DSR1G</b>	<b>A4</b>
<b>DSR1J</b>	<b>A5</b>
<b>DSR1k</b>	<b>A6</b>
<b>DSR1M</b>	<b>A7</b>

Parameter	Symbols	DSR1A	DSR1B	DSR1D	DSR1G	DSR1J	DSR1K	DSR1M	Units
Maximum Repetitive Peak Reverse Voltage	<b>V<sub>RRM</sub></b>	50	100	200	400	600	800	1000	<b>V</b>
Maximum RMS voltage	<b>V<sub>RMS</sub></b>	35	70	140	280	420	560	700	<b>V</b>
Maximum DC Blocking Voltage	<b>V<sub>DC</sub></b>	50	100	200	400	600	800	1000	<b>V</b>
Maximum Average Forward Rectified Current at T <sub>c</sub> = 125 °C	<b>I<sub>F(AV)</sub></b>					1			<b>A</b>
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	<b>I<sub>FSM</sub></b>					30			<b>A</b>
Maximum Instantaneous Forward Voltage at 1 A	<b>V<sub>F</sub></b>				1.1				<b>V</b>
Maximum DC Reverse Current T <sub>a</sub> = 25 °C at Rated DC Blocking Voltage T <sub>a</sub> =125 °C	<b>I<sub>R</sub></b>				5	50			<b>µA</b>
Typical Junction Capacitance <sup>(1)</sup>	<b>C<sub>j</sub></b>				11				<b>pF</b>
Typical Thermal Resistance <sup>(2)</sup>	<b>R<sub>θJA</sub></b>				90				<b>°C/W</b>
Operating and Storage Temperature Range	<b>T<sub>j</sub> T<sub>stg</sub></b>				-55 ~ +150				<b>°C</b>


(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Instantaneous Reverse Characteristics**




**Fig.3 Typical Forward Characteristic**




**Fig.4 Typical Junction Capacitance**




**Fig.5 Maximum Non-Repetitive Peak Forward Surge Current**



**Package Outline**
**SOD-123FL**
**Plastic surface mounted package; 2leads**


UNIT		A	C	D	E	e	g	H <sub>E</sub>	θ
mm	max	1.3	0.20	2.9	1.9	1.1	0.9	3.8	7°
	min	0.9	0.12	2.6	1.7	0.8	0.7	3.5	
mil	max	43	7.9	114	75	43	35	150	7°
	min	35	4.7	102	67	31	28	138	

**The recommended mounting pad size**

Unit:  $\frac{\text{mm}}{(\text{mil})}$ 
**Summary of Packing Options**

Package	Packing Description	Packing Quantity	Industry Standard
SOD-123FL	Tape/Reel, 13" reel	10000	EIA-481-1
	Tape/Reel, 7" reel	3000	EIA-481-1