

PCB terminal, Screw connection, No. of poles: 21, Width: 73.9 mm, Colour: Green

### Business data

|  |                     |
|--|---------------------|
| Article number                             | <u>14142.1</u>      |
| Article name                               | PK 601/21/3,50-V GN |
| GTIN (EAN)                                 | 4044211174644       |
| Packaging unit                             | 50                  |
| Quantity unit                              | PC                  |
| Packaging type                             | Carton              |
| Type of banding                            | Without             |
| Weight per piece (not including packaging) | 11.64 g             |
| Weight per piece (including packaging)     | 12.89 g             |
| Unit of weight                             | G                   |
| Customs number                             | 85369010            |
| Country of origin                          | QU                  |
| Colour                                     | Green               |

---

### Technical data

---

#### Dimensions

|                            |         |
|----------------------------|---------|
| Length                     | 7.4 mm  |
| Length of the pin          | 3.8 mm  |
| Width                      | 73.9 mm |
| Width left                 | 2.15 mm |
| Width right                | 1.75 mm |
| Height                     | 8.5 mm  |
| Drill hole diameter        | 1.2 mm  |
| Diameter of connecting pin | 0.9 mm  |
| Pitch                      | 3.5 mm  |

#### Ratings

|                       |                   |
|-----------------------|-------------------|
| Rated voltage         | 130 V             |
| Rated current         | 10 A              |
| Rated cross-section   | 1 mm <sup>2</sup> |
| Rated impulse voltage | 1.25 kV           |
| Overvoltage category  | III               |
| Contamination degree  | 3                 |

### Technical data

#### Connection data

|   |                      |
|---|----------------------|
| Connection principle                                    | Screw connection     |
| Connection type of PCB                                  | Solder connection    |
| Type of attachment to circuit board                     | Connecting contact   |
| Angle of PCB/wire connection                            | 0°/180° (horizontal) |
| No. of poles  | 21                   |
| Number of levels  | 1                    |
| Wire cross-section single-core (rigid) / stranded, min. | 0.08 mm <sup>2</sup> |
| Wire cross-section single core (rigid)/stranded, max.   | 1.5 mm <sup>2</sup>  |
| Wire cross-section stranded, min.                       | 0.08 mm <sup>2</sup> |
| Wire cross-section stranded, max.                       | 1 mm <sup>2</sup>    |
| Wire cross-section stranded with wire-end ferrules,min. | 0.14 mm <sup>2</sup> |
| Wire cross-section stranded with wire-end ferrules,max. | 0.34 mm <sup>2</sup> |
| Wire cross-section AWG, min.                            | 28                   |
| Wire cross-section AWG, max.                            | 16                   |
| Stripping length  | 6 mm                 |
| Screw threading   | M 2                  |
| Torque  | 0.2 Nm               |

#### Materials

|                           |               |
|---------------------------|---------------|
| Insulation housing        | Polyamide 6.6 |
| Flammability class UL 94  | V-0           |
| Working temperature, min. | -30 °C        |
| Working temperature, max. | 105 °C        |
| Clamping element          | Brass         |
| Screws                    | Steel         |
| Soldering lug             | Brass         |

### Technical data

#### Further technical data

|  |                             |
|--|-----------------------------|
| Storage temperature, min.                      | -40 °C                      |
| Storage temperature, max.                      | 105 °C                      |
| Insulation resistance                          | 1*10 <sup>13</sup> Ohm x cm |
| Creepage-current resistance                    | CTI 600                     |
| Glow wire flammability index GWFI              | GWFI 850                    |
| GWFI after-glow time                           | 30 Sek.                     |
| Glow wire ignition temperature GWIT            | GWIT 775 °C                 |
| GWIT exposure time                             | 5 Sek.                      |
| Connection cycles, in compliance with standard | 5                           |
| Recommended wave soldering temperature         | 265 °C                      |
| Recommended wave soldering duration, min.      | 3 Sek.                      |
| Recommended wave soldering duration, max.      | 4 Sek.                      |

#### Environmental Product Compliance

|                                |            |
|--------------------------------|------------|
| REACH Conform                  | No         |
| REACH Reference date           | 2023-06-14 |
| REACH Candidate Substance Note | No         |
| REACH CAS 1 Substance          | LEAD       |
| REACH CAS 1 Percent minimal    | 0.1 %      |
| REACH CAS 1 Percent maximum    | 4 %        |
| REACH CAS 1 Number             | 7439-92-1  |
| RoHS Conform                   | yes        |
| RoHS Exception rule            | 6c         |

### Approvals

#### cUL Recognized

|  |                |
|--|----------------|
| cUL approval   | C22.2 No 158   |
| cUL Usegroup B: rated voltage                        | 150 V          |
| cUL Usegroup B: rated current                        | 10 A           |
| cUL wire cross-section single-core (rigid) AWG, min. | 28             |
| cUL wire cross-section single-core (rigid) AWG, max. | 16             |
| cUL wire cross-section stranded AWG, min.            | 28             |
| cUL wire cross-section stranded AWG, max.            | 16             |
| cUL torque   | 0.200000003 Nm |
| cUL wire material                                    | Cu             |
| cUL Recognized                                       | 1              |

#### UL Recognized

|   |            |
|---|------------|
| UL approval   | UL 1059    |
| UL Usegroup B: rated voltage                        | 150 V      |
| UL Usegroup B: rated current                        | 10 A       |
| UL wire cross-section single-core (rigid) AWG, min. | 28         |
| UL wire cross-section single-core (rigid) AWG, max. | 16         |
| UL wire cross-section stranded AWG, min.            | 28         |
| UL wire cross-section stranded AWG, max.            | 16         |
| UL torque   | 1.77 Lb In |
| UL wire material                                    | Cu         |
| UL factory wiring                                   | 1          |
| UL field wiring                                     | 1          |
| UL Recognized                                       | 1          |




### Approvals

#### VDE approval

|   |                     |
|---|---------------------|
| VDE approval  | DIN EN 60998        |
| VDE approval granted                                | yes                 |
| VDE rated voltage                                   | 130 V               |
| VDE rated current                                   | 10 A                |
| VDE rated current wire cross-section rigid, max.    | 10 A                |
| VDE rated current wire cross-section stranded, max. | 10 A                |
| VDE rated impulse voltage                           | 1.25 kV             |
| VDE wire cross-section rigid, min.                  | 0.2 mm <sup>2</sup> |
| VDE wire cross-section rigid, max.                  | 1 mm <sup>2</sup>   |
| VDE wire cross-section stranded, min.               | 0.2 mm <sup>2</sup> |
| VDE wire cross-section stranded, max.               | 1 mm <sup>2</sup>   |
| VDE screw threading                                 | M 2                 |
| VDE torque  | 0.2 Nm              |
| VDE overvoltage category                            | III                 |
| VDE contamination degree                            | 3                   |

### Media

# M2



---

### Accessories

---