SIEMENS

Data sheet


3SE5132-0PD05



Position switch Plastic enclosure 40 mm according to EN 50041 Device connection 1x (M20 x 1.5) 2 NO/1 NC slow-action contacts Roller plunger, plastic with plastic roller 13 mm

· · · · ·	
product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
 of the supplied basic switch 	<u>3SE5132-0PA00</u>
 of the supplied actuator head for position switches 	<u>3SE5000-0AD05</u>
 of the supplied switching contacts 	<u>3SE5000-0PA00</u>
 of the supplied empty enclosure with cover 	<u>3SE5132-0AA00</u>
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	250 V
degree of pollution	class 3
surge voltage resistance rated value	4 kV
protection class IP	IP66/IP67
shock resistance	
according to IEC 60068-2-27	30g / 11 ms
vibration resistance according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
material of the enclosure of the switch head	plastic
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	116.3 mm
width of the sensor	40 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz

e during storage explosion protection category for dust Installation/ mounting/ dimensions mounting position fastening method Certificates/ approvals General Product Approval Confirmati	any screw fixing ERE ERE
explosion protection category for dust Installation/ mounting/ dimensions mounting position fastening method Certificates/ approvals	any
explosion protection category for dust Installation/ mounting/ dimensions mounting position fastening method Certificates/ approvals	any
explosion protection category for dust Installation/ mounting/ dimensions mounting position fastening method	any
explosion protection category for dust Installation/ mounting/ dimensions mounting position	any
explosion protection category for dust Installation/ mounting/ dimensions	
explosion protection category for dust	none
e during storage	-40 +90 °C
during operation	-25 +85 °C
ambient temperature	05
Ambient conditions	
design of the interface	without
Communication/ Protocol	
cable entry type	1x (M20 x 1.5)
at AWG cables stranded	1x (20 16), 2x (20 18)
at AWG cables solid	1x (20 16), 2x (20 18)
• finely stranded with core end processing	1x (0.5 1.5 mm ²), 2x (0.5 0.75 mm ²)
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
type of connectable conductor cross-sections	
type of electrical connection	screw-type terminals
Connections/ Terminals	
number of switching contacts safety-related	1
circuit principle	slow-action contacts
design of the switching function	positive opening
shape of the switch head	roller
standard-compliant actuator head	EN 50041, design C
design of the actuating element	Roller plunger, plastic roller
Drive Head	
design of the housing according to standard	Yes
coating of the enclosure	Other types
material of the enclosure	plastic
design of the housing	block, narrow
Enclosure	
design of the interface for safety-related communication	without
• at 400 V rated value	0.12 A
• at 250 V rated value	0.27 A
• at 125 V rated value	0.55 A
at 24 V rated value	3 A
operational current at DC-13	
• at 400 V rated value	4 A
at 240 V rated value	6 A
at 125 V rated value	6 A
at 24 V rated value	6 A
operational current at AC-15	2
number of NC contacts for auxiliary contacts number of NO contacts for auxiliary contacts operational current at AC-15	1





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5132-0PD05


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5132-0PD05

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5132-0PD05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5132-0PD05&lang=en



last modified:

12/21/2020 🖸