## SIEMENS

## Data sheet

## 3SE5423-0CC21-1EA2



Position switch in compact design 40 mm wide with connection cable 2 m Snap-action contacts 1 NO+1 NC Rounded plunger with central mounting

979			
product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	3		
surge voltage resistance rated value	4 kV		
protection class IP	IP67		
shock resistance			
<ul> <li>according to IEC 60068-2-27</li> </ul>	30g / 11 ms		
vibration resistance according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	10 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	500 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	1 800		
thermal current	10 A		
material of the enclosure of the switch head	metal		
reference code according to IEC 81346-2	В		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	20 N		
length of the sensor	60 mm		
width of the sensor	40 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	1		
number of NO contacts for auxiliary contacts	1		
operational current at AC-15			
• at 125 V rated value	6 A		
• at 230 V rated value	3 A		
operational current at DC-13			
• at 125 V rated value	0.55 A		
• at 230 V rated value	0.27 A		

Confirmation FA	r far	CE	UK
General Product Approval		Declaration of Cor	nformity
Certificates/ approvals			
fastening method	screw fixing		
mounting position	any		
nstallation/ mounting/ dimensions			
explosion protection category for dust	none		
during storage	-25 +85 °C		
during operation	-25 +85 °C		
ambient temperature			
Ambient conditions	WithOut		
design of the interface	without		
type of electrical connection Communication/ Protocol	cable, 5 x 0.75mm <sup>2</sup>		
Connections/ Terminals	$aabla 5 \times 0.75 mm^2$		
number of switching contacts safety-related	1		
circuit principle	snap-action contacts		
design of the switching function	snap-action contact		
shape of the switch head	rounded		
design of the actuating element	rounded plunger		
Drive Head	-		
material of cable sheath	PVC		
design of the housing according to standard	No		
coating of the enclosure	painted		
material of the enclosure	metal		
design of the housing	block		
design of the interface for safety-related communication Enclosure	without		

other

**Confirmation** 

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5423-0CC21-1EA2

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5423-0CC21-1EA2

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5423-0CC21-1EA2

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SE5423-0CC21-1EA2&lang=en

last modified:

1/26/2022 🖸