

FilterCap MKD AC – Single phase

Series/Type: B32373 Series Ordering code: B32373A5137J300

Date: Version: 2017-12-26 2

© EPCOS AG 2017. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

IDK

B32373A5137J300

B32373 Series

Film capacitors - Power Electronic Capacitors

FilterCap MKD AC – Single phase

Preliminary data

Construction

- Metallized Polypropylene Film
- Non-PCB, Soft Polyurethane resin
- Extruded round aluminium can with stud, Aluminium top cover, DMC leadthrough

Features

- Safety system:
 - overpressure disconnector,
 - self healing technology
- Naturally air cooled (or forced air cooling)
- Indoor mounting

Terminals

- M10 Screw terminals Nut: M10, DIN934, (max. torque for terminals=10Nm), Washer: M6, DIN125,
- Max.current of terminal 60A

Mounting

Threaded stud M12 at bottom of can (max. torque for M12 = 12 Nm)



Drawing just for reference

Characteristics			
C _N	133	μF	
Tol.	±5	%	
U _{RMS}	500	Vac	
U _N	710	Vac	
I _{max} (*)	60	A	
Rs	1.4	mΩ	
Tanδ₀	2×10 ⁻⁴		

* Including combined effects of harmonics(<20kHz), over voltages, capacitance tolerance and hot spot(≤85 °C, ambient temperature 70 °C). Higher Imax is possible on request at lower ambient temperatures

Please read Cautions and warnings and



FilterCap MKD AC – Single phase

B32373A5137J300

B32373 Series

Preliminary data

Maximum ratings				
Î	2,550	A		
Is	7,650	A		
(du/dt) _{max}	19	V/µs		
(du/dt)s	57	V/µs	V/µs	
U _{max}	1.1×U _{RMS}	8hr/day	8hr/day	
	1.2×U _{RMS}	5min/day	5min/day	
	1.3×U _{RMS}	,	1min/day	
Test data				
	1,075	Vac	2s	
UTC	4,000	Vac		
R _{is} ×C	≥10,000	s	105	
Tan δ _(1kHz)	≤3.0×10 ⁻³			
Tanδ _(100Hz)	≤1.0×10 ⁻³			
	40/70/21			
Climatic category (IEC68-1)				
Θ_{\min}	-40	°C		
Θ _{max} **	+70	°C		
Θ _{HS}	+85	°C		
Θ _{stg}	-40+85	°C		
Average Rel. Humidity	≤95%			
t _{LD (co)}	100,000	h		
α _{FQ (co)}	50	Fit		
Max.altitude	2,000	m		
General data				
Weight	1.5	Kg		
Packing unit	4	PCS		
Creepage Distance	Min.12.7mm	I		
Clearance Distance	Min.10.0mm			
Mounting position	** Considering mounting positon with terminals to The top.			
	For other mounting position, please Request evaluation			
Safety				
Mechanical safety***	Overpressure disconnector			
Max.short circuit current	10k AFC			
Reference standard				
IEC 61071, UL810 ed5 th .edition				
Certification				
UL file No.E487229,CSA C22.2,No.1	90-14			

UL file No.E487229,CSA C22.2,No.190-14

*** When the over pressure disconnector respond, the capacitor extends up to max.12.7mm, so leave




B32373A5137J300 B32373 Series

FilterCap MKD AC – Single phase

Preliminary data

sufficient space min. 15mm above the terminals when mounting the capacitor.

Dimensional drawings





B32373A5137J300

B32373 Series

Film capacitors - Power Electronic Capacitors

FilterCap MKD AC – Single phase

Preliminary data

Label information



The Date code and Bar code explanation are following:

'WW Z YYYY', where:

'WW' means production weeks(ex.:25)

'Z' means Zhuhai (China)


'YYYY' means production years(ex.:2017)

Bar code consists of batch number and serial number.

Batch number : 9 digits(ex.:123456789)

Serial number : 3 digits(ex.:001)

Expected Lifetime





B32373A5137J300 B32373 Series

FilterCap MKD AC – Single phase

Preliminary data

Cautions and warnings

- In case of dents of more than 1 mm depth or any other mechanical damage, capacitor must not be used at all.
- Check tightness of the connections / terminals periodically.
- The energy stored in capacitors may be lethal. To prevent any chance of shock, discharge and short-circuit the capacitors before handling.
- Failure to follow cautions may results, worst case, in premature failures, bursting and fire.

Safety

- Electrical or mechanical misapplication of capacitors may be hazardous. Personal injury or property damage may result from bursting of the capacitor or from expulsion of melted material due to mechanical disruption of the capacitor.
- Ensure good, effective grounding for capacitor enclosures.
- Observe appropriate safety precautions during operation (self-recharging phenomena and the high energy stored in capacitors).
- Handle capacitors carefully, because they may still be charged even after disconnection.
- The terminals of capacitors, connected bus bars and cables as well as other devices may also be energized.
- Follow good engineering practice.
- The maximum allowed fault current (AFC) of 10kA in accordance with UL 810 standard must be assured by the application.

Thermal load

After installation of the capacitor it is necessary to verify that maximum hot-spot temperature is not exceed at extreme service conditions.

Mechanical protection

The capacitor has to be installed in a way that mechanical damages and dents in the case are avoided.

Storage and operating conditions

Do not use or store capacitors in corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. In dusty environments regular maintenance and cleaning especially of the terminals is required to avoid conductive path between phases and/or phases and ground.

Overpressure disconnector

- To ensure full functionality of an overpressure safety device disconnector, the following must be observed:
 - 1. The elastic elements must not be hindered, i.e.
 - Connecting lines must be flexible leads (cables)
 - There must be sufficient space (min.15mm) for expansion above the connections
 - Metal cover must not be retained by rigid parts, like: bus bars.
 - 2. Stress parameters of the capacitor must be within the IEC 61071 specification.

Service life expectancy

Electrical components do not have an unlimited service life expectancy; this applies to self-healing capacitors too. The maximum service life expectancy may vary depending on the application the capacitor is used in.

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.