## **SIEMENS**

## **Data sheet**

## 3SE5242-0HK62-1AJ0



Position switch Plastic 50 mm Increased corrosion protection Device connection 2x (M20x 1.5) 1 NO/1 NC snap-action contacts adjustable-length Twist lever, Stainless steel lever with plastic roller 19 mm functional at -40 °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
<ul> <li>of the supplied actuator head for position switches</li> </ul>	3SE5000-0AK00-1AJ0
<ul> <li>of the supplied operating lever</li> </ul>	3SE5000-0AA62-1AJ0
suitability for use safety switch	Yes
General technical data	
product function positive opening	No
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
<ul> <li>according to IEC 60068-2-27</li> </ul>	30g / 11 ms
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B
vibration resistance	
<ul><li>according to IEC 60068-2-6</li></ul>	0.35 mm/5g
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
material of the enclosure of the switch head	plastic
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating torque in directions of actuation	0.25 N·m
length of the sensor	182 mm
width of the sensor	50 mm
design of the switching contact	mechanical

operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current at AC-15	
at 24 V rated value	6 A
at 120 V rated value	6 A
• at 240 V rated value	6 A
at 400 V rated value	4 A
operational current at DC-13	
at 24 V rated value	3 A
at 125 V rated value	0.55 A
• at 250 V rated value	0.27 A
• at 400 V rated value	0.12 A
design of the interface for safety-related communication	without
Enclosure	
design of the housing	block, wide
material of the enclosure	plastic
coating of the enclosure	Other types
design of the housing according to standard	No
Drive Head	
design of the actuating element	Adjustable twist lever, adjustable-length metal lever with positive fit, 100 mm long, plastic roller 19 mm
standard-compliant actuator head	EN 50047, design A
shape of the switch head	roller
design of the switching function	positive opening, integrated
circuit principle	snap-action contacts
number of switching contacts safety-related	0
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
finely stranded with core end processing	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
at AWG cables solid	1x (20 16), 2x (20 18)
at AWG cables stranded	1x (20 16), 2x (20 18)
cable entry type	1x (M20 x 1.5)
Communication/ Protocol	W
design of the interface	without
Ambient conditions	
ambient temperature	40 105 °C
during operation	-40 +85 °C
during storage     explosion protection category for dust	40 +90 °C
	none
Installation/ mounting/ dimensions	any
mounting position fastening method	any screw fiving
Certificates/ approvals	screw fixing
General Product Approval	



Confirmation











Type Test Certificates/Test Report

Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5242-0HK62-1AJ0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5242-0HK62-1AJ0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) <a href="https://support.industry.siemens.com/cs/ww/en/ps/3SE5242-0HK62-1AJ0">https://support.industry.siemens.com/cs/ww/en/ps/3SE5242-0HK62-1AJ0</a>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SE5242-0HK62-1AJ0&lang=en

last modified:	3/23/2022
iast illouillea.	3/23/2022