

R75TR315050L3J

Aliases (75TR315050L3J)

R75, Film, Metallized Polypropylene, General Purpose, 0.15 uF, 5%, 1600 VDC, 85°C, Lead Spacing = 27.5mm



Click [here](#) for the 3D model.

Dimensions

L	32mm +0.3/-0.7mm
H	15mm +0.1/-0.7mm
T	24mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	144

General Information

Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	11.9 g
Miscellaneous	Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C.

Specifications

Capacitance	0.15 uF
Capacitance Tolerance	5%
Voltage AC	650 VAC
Voltage DC	1600 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	1500 V/us
Resistance	7.427 mOhms (100kHz)
Ripple Current	9.962 Amps (100kHz 85C), 225 Amps (Peak)
Inductance	18 nH