SIEMENS

Data sheet

3SE5162-0BA00-1CA0



Basic switch for position switch 3SE5162 Metal enclosure XL, 56 mm wide Device connection $3x(M20 \times 1.5)$ IP66/IP67 2 x (1 NO/2 NC) Slow-action contacts without actuator head with increased corrosion protection

product brand name	SIRIUS		
product designation	Mechanical safety switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	1x 3SE5000-0BA00, 1x 3SE5060-0BA00		
 of the supplied empty enclosure with cover 	3SE5162-0AA00-1CA0, on request		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	class 3		
surge voltage resistance rated value	6 kV		
protection class IP	IP66/IP67		
shock resistance			
 according to IEC 60068-2-27 	30g / 11 ms		
vibration resistance according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	5 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	5 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	30 N		
length of the sensor	107.7 mm		
width of the sensor	56 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	2		
number of NO contacts for auxiliary contacts	2		
operational current at AC-15			

 at 24 V rated value 	6 A			
 at 125 V rated value 	6 A			
 at 240 V rated value 	6 A			
• at 400 V rated value	4 A			
operational current at DC-13				
 at 24 V rated value 	3 A			
 at 125 V rated value 	0.55 A			
 at 250 V rated value 	0.27 A			
 at 400 V rated value 	0.12 A			
design of the interface for safety-related communication	without			
Enclosure				
design of the housing	block, wide			
material of the enclosure	metal			
coating of the enclosure	cathodic dip coating			
design of the housing according to standard	No			
Drive Head				
design of the actuating element	Other without basis switch			
	Other, without, basic switch			
design of the switching function	Positive opening with appropriate positive opening actuator head			
circuit principle	slow-action contacts	slow-action contacts		
number of switching contacts safety-related	2			
Connections/ Terminals				
type of electrical connection	screw-type terminals			
type of connectable conductor cross-sections				
• solid	1x (0.5 1.5 mm ²), 2x (0.5 0.75 mm ²)			
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)			
 at AWG cables solid 	1x (20 16), 2x (20 18)			
at AWG cables stranded	1x (20 16), 2x (20 18)			
cable entry type	3x (M20 x 1.5)			
Communication/ Protocol				
design of the interface	without			
Ambient conditions				
ambient temperature				
 during operation 	-25 +85 °C			
during storage	-40 +90 °C			
explosion protection category for dust	none			
Installation/ mounting/ dimensions				
mounting position	any			
fastening method	screw fixing			
Certificates/ approvals	Sorew Inxing			
General Product Approval				
Confirmation	<u>"</u>	r N r	r N r	
	(ŸL)	FAL	FHI	
CSA CCC	UL	LIIL	LIIL	
Functional Safety/Safety of Declaration of Conformity	Test Certificates	other		
Machinery	rest certificates	other		
Type Examination	Type Test Certific-	Confirmation		
Type Examination CertificateCE EG-Konf.UK CE	ates/Test Report			
EG-Konf.	1			

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5162-0BA00-1CA0


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5162-0BA00-1CA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5162-0BA00-1CA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5162-0BA00-1CA0&lang=en





last modified:

3/23/2022 🖸