SIEMENS

Data sheet 3SE5122-0LC02



Position switch Metal enclosure 56 mm wide Device connection 3x (M20x 1.5) 1 NO/2 NC quick action contacts Rounded plunger with overtravel made of stainless steel

product brand name	SIRIUS	
product designation	Mechanical position switches	
product type designation	3SE5	
manufacturer's article number		
 of the supplied basic switch 	3SE5122-0LA00	
 of the supplied actuator head for position switches 	3SE5000-0AC02	
 of the supplied switching contacts 	3SE5000-0LA00	
 of the supplied empty enclosure with cover 	3SE5122-0AA00	
suitability for use safety switch	Yes	
General technical data		
product function positive opening	Yes	
insulation voltage rated value	400 V	
degree of pollution	class 3	
surge voltage resistance rated value	6 kV	
protection class IP	IP66/IP67	
shock resistance		
• according to IEC 60068-2-27	30g / 11 ms	
vibration resistance according to IEC 60068-2-6	0.35 mm/5g	
mechanical service life (switching cycles) typical	15 000 000	
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000	
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000	
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000	
thermal current	10 A	
material of the enclosure of the switch head	metal	
reference code according to IEC 81346-2	В	
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A	
continuous current of the DIAZED fuse link gG	6 A	
active principle	mechanical	
repeat accuracy	0.05 mm	
Substance Prohibitance (Date)	07/01/2006	
minimum actuating force in directions of actuation	20 N	
length of the sensor	103.5 mm	
width of the sensor	56 mm	
design of the switching contact	mechanical	
operating frequency rated value	50 60 Hz	

number of NC contacts for conflicts contacts	2		
number of NC contacts for auxiliary contacts	2		
number of NO contacts for auxiliary contacts	1		
operational current at AC-15			
at 24 V rated value	6 A		
• at 125 V rated value	6 A		
• at 240 V rated value	6 A		
at 400 V rated value	4 A		
operational current at DC-13			
at 24 V rated value	3 A		
• at 125 V rated value	0.55 A		
at 250 V rated value	0.27 A		
at 400 V rated value	0.12 A		
design of the interface for safety-related communication	without		
Enclosure			
design of the housing	block, wide		
material of the enclosure	metal		
coating of the enclosure	cathodic dip coating		
design of the housing according to standard	No		
Drive Head			
design of the actuating element	Rounded plunger, high-grade steel plunger		
standard-compliant actuator head	EN 50041, design B		
shape of the switch head	rounded		
design of the switching function	positive opening		
circuit principle	snap-action contacts		
number of switching contacts safety-related	2		
Connections/ Terminals			
type of electrical connection	screw-type terminals		
type of connectable conductor cross-sections			
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 at AWG cables solid 	1x (20 16), 2x (20 18)		
 at AWG cables stranded 	1x (20 16), 2x (20 18)		
cable entry type	3x (M20 x 1.5)		
Communication/ Protocol			
design of the interface	without		
Ambient conditions			
ambient temperature			
during operation	-25 +85 °C		
during storage	-40 +90 °C		
explosion protection category for dust	none		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
Certificates/ approvals			
General Product Approval			





Confirmation







Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates	other
---	-------------------	-------





Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5122-0LC02

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5122-0LC02

 ${\bf Service \& Support\ (Manuals,\ Certificates,\ Characteristics,\ FAQs,...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3SE5122-0LC02

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5122-0LC02&lang=en