3SE5214-0CC05-1AC5

## **Data sheet**



position switch metal enclosure according to EN 50047, 31 mm 1 NO/1 NC quick action contacts with M12 plug, 5-pole pin assignment: Pin1=21, Pin2=22 Pin3=13, Pin4=14, Pin5=PE for maximum 125 V and 4 A with plunger

product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
<ul> <li>of the supplied switching contacts</li> </ul>	3SE5000-0CA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	125 V
degree of pollution	class 3
surge voltage resistance rated value	2 kV
protection class IP	IP66/IP67
shock resistance	
• according to IEC 60068-2-27	30g / 11 ms
vibration resistance	
<ul><li>according to IEC 60068-2-6</li></ul>	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	4 A
material of the enclosure of the switch head	metal
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	4 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	4 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	75.7 mm
width of the sensor	31 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current at AC-15	
at 24 V rated value	4 A

• at 125 V rated value	4 A
operational current at DC-13	
<ul><li>at 24 V rated value</li></ul>	3 A
at 125 V rated value	0.55 A
design of the interface for safety-related communication	without
Enclosure	
design of the housing	block, narrow
material of the enclosure	metal
coating of the enclosure	cathodic dip coating
design of the housing according to standard	Yes
Drive Head	
design of the actuating element	Rounded plunger, plastic plunger
standard-compliant actuator head	EN 50047, design B
shape of the switch head	rounded
design of the switching function	positive opening
circuit principle	snap-action contacts
number of switching contacts safety-related	1
Connections/ Terminals	
type of electrical connection	M12 plug, fixed
cable entry type	1x (M20 x 1.5)
design of plug-in connection	M12 connector, 5-pole: pin 1= terminal 21, pin 2= 22, pin 3= 13, pin 4=
accigi. c. play iii cominoulon	14, pin 5= PE
Communication/ Protocol	
Communication/ Protocol	14, pin 5= PE
Communication/ Protocol design of the interface	14, pin 5= PE
Communication/ Protocol design of the interface Ambient conditions	14, pin 5= PE
Communication/ Protocol  design of the interface  Ambient conditions  ambient temperature	14, pin 5= PE  without
Communication/ Protocol design of the interface Ambient conditions ambient temperature • during operation	14, pin 5= PE  without  -25 +85 °C
Communication/ Protocol  design of the interface  Ambient conditions  ambient temperature  • during operation  • during storage	14, pin 5= PE  without  -25 +85 °C  -40 +90 °C
Communication/ Protocol  design of the interface  Ambient conditions  ambient temperature  • during operation • during storage  explosion protection category for dust	14, pin 5= PE  without  -25 +85 °C  -40 +90 °C
Communication/ Protocol  design of the interface  Ambient conditions  ambient temperature  • during operation  • during storage  explosion protection category for dust  Installation/ mounting/ dimensions	14, pin 5= PE  without  -25 +85 °C  -40 +90 °C  none
Communication/ Protocol design of the interface Ambient conditions ambient temperature	14, pin 5= PE  without  -25 +85 °C  -40 +90 °C  none  any



Confirmation









Functional	
Safety/Safety of	- 1
Machinery	

**Declaration of Conformity** 

**Test Certificates** 

other

Type Examination Certificate





Type Test Certificates/Test Report

Type Test Certificates/Test Report

Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5214-0CC05-1AC5

Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5214-0CC05-1AC5


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3SE5214-0CC05-1AC5

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SE5214-0CC05-1AC5&lang=en







last modified:

3/23/2022