## **SIEMENS**

Data sheet 3SE5132-0CA00



Basic switch for position switch 3SE513 Enclosure plastic according to EN 50041, 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts without actuator head

product brand name	SIRIUS
product designation	Mechanical safety switches
product type designation	3SE5
manufacturer's article number	
<ul> <li>of the supplied switching contacts</li> </ul>	3SE5000-0CA00
of the supplied empty enclosure with cover	3SE5132-0AA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
according to IEC 60068-2-27	30g / 11 ms
vibration resistance according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	85.7 mm
width of the sensor	40 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current at AC-15	

• at 24 V rated value	6 A
• at 125 V rated value	6 A
<ul> <li>at 240 V rated value</li> </ul>	6 A
<ul> <li>at 400 V rated value</li> </ul>	4 A
operational current at DC-13	
<ul><li>at 24 V rated value</li></ul>	3 A
<ul> <li>at 125 V rated value</li> </ul>	0.55 A
<ul> <li>at 250 V rated value</li> </ul>	0.27 A
at 400 V rated value	0.12 A
design of the interface for safety-related communication	without
Enclosure	
design of the housing	block, narrow
material of the enclosure	plastic
coating of the enclosure	Other types
design of the housing according to standard	Yes
Drive Head	
design of the actuating element	Other, without, basic switch
design of the switching function	Positive opening with appropriate positive opening actuator head
circuit principle	snap-action contacts
number of switching contacts safety-related	1
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
<ul> <li>at AWG cables solid</li> </ul>	1x (20 16), 2x (20 18)
at AWG cables stranded	1x (20 16), 2x (20 18)
cable entry type	1x (M20 x 1.5)
Communication/ Protocol	
design of the interface	without
Ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +85 °C
during storage	-40 +90 °C
explosion protection category for dust	none
Installation/ mounting/ dimensions	
mounting position	any
mounting position fastening method	any screw fixing





Confirmation







Functional Safety/Safety of Machinery

**Declaration of Conformity** 

other

Type Examination Certificate





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) <a href="https://www.siemens.com/ic10">https://www.siemens.com/ic10</a>

Industry Mall (Online ordering system)


https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5132-0CA00

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5132-0CA00

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5132-0CA00

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax">http://www.automation.siemens.com/bilddb/cax</a> de.aspx?mlfb=3SE5132-0CA00&lang=en



last modified: 3/23/2022 🖸