EMC Components

Noise suppression filter For audio lines (For Bluetooth Band, WiFi Band) MAF series



FEATURES

O A compact noise suppression component for audio lines that accommodates high currents.

- Small reductions in volume due to its low resistance, and optimal for devices that require high sound quality as the generating of sound distortions is controlled.
- O It is highly effective in suppressing harmonic noise (Bluetooth, WiFi, cellular band) by a Class-D amplifier.

○ Operating temperature range: -55 to +125°C

MAF0603FA type

APPLICATION

Sound lines for devices such as TWS(True Wireless Stereo), Bluetooth headset, headset, smartphones, tablets and wearable equipments (earphones, microphones, and speakers).

○ Sound lines for portable game machines.

PART NUMBER CONSTRUCTION

MAF	0603	F	AL	470	В	Т	000
Series name	L×W×T dimensions 0.6×0.3x0.3 mm	Characteristics	Internal code	Impedance (Ω) at 100MHz	Туре	Packaging style	Internal code

CHARACTERISTICS SPECIFICATION TABLE

Impedance		DC resistance	Rated current	Part No.
[100MHz]				
(Ω)	Tolerance	(Ω)max.	(mA)max.	
33	±25%	0.70	200	MAF0603FAL330BT000
47	±25%	0.70	200	MAF0603FAL470BT000

Measurement equipment

Measurement item	Product No.	Manufacturer		
Impedance	4991A+16197A	Keysight Technologies		
DC resistance	Type-755611	Yokogawa		
* Equivalent measurement equipment may be used				


* Equivalent measurement equipment may be used.

⊗TDK




MAF0603FA type

Z FREQUENCY CHARACTERISTICS



* Equivalent measurement equipment may be used.


■ INSERTION LOSS VS. FREQUENCY CHARACTERISTICS



A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (2/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.


MAF0603FA type

SHAPE & DIMENSIONS




Dimensions in mm

PACKAGING STYLE




Dimensions in mm

TAPE DIMENSIONS



Туре	А	В	К
MAF0603FA	0.38±0.05	0.68±0.05	0.5max.



Dimensions in mm

PACKAGE QUANTITY


Package quantity 15,000 pcs/reel

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight	
–55 to +125°C	–55 to +125°C	0.3 mg	
The storage temperature range is for after the assembly			

ature range is for after the a

RECOMMENDED LAND PATTERN



RECOMMENDED REFLOW PROFILE


Preheating

60 to 120s

Temperature

150°C

Dimensions in mm



Natural

cooling

230°C

Soldering

Peak 250 to 260°C

10s

30 to 60s

230°C

180°C

Time

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

 The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH c less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. 				
Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).				
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature does not exceed 150°C. 	re difference between the solder temperature and chip temperature			
\supset Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.				
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.				
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set therma design.				
 Carefully lay out the coil for the circuit board design of the non-mag A malfunction may occur due to magnetic interference. 	gnetic shield type.			
\bigcirc Use a wrist band to discharge static electricity in your body through	h the grounding wire.			
\bigcirc Do not expose the products to magnets or magnetic fields.				
\bigcirc Do not use for a purpose outside of the contents regulated in the d	lelivery specifications.			
ment, industrial robots) under a normal operation and use conditio The products are not designed or warranted to meet the requirement ity require a more stringent level of safety or reliability, or whose far person or property.	ment, personal equipment, office equipment, measurement equip-			
 (1) Aerospace/aviation equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (3) Medical equipment (4) Power-generation control equipment (5) Atomic energy-related equipment (6) Seabed equipment (7) Transportation control equipment When designing your equipment even for general-purpose application tection circuit/device or providing backup circuits in your equipment.	 (8) Public information-processing equipment (9) Military equipment (10) Electric heating apparatus, burning equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (13) Other applications that are not considered general-purpose applications 			

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.