SIEMENS

Data sheet

3SE5232-0CC05-1AJ0



Position switch Plastic 31 mm according to EN 50047 Increased corrosion protection Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts Rounded plunger functional at -40 °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	<u>3SE5000-0CA00</u>		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	class 3		
surge voltage resistance rated value	6 kV		
protection class IP	IP65		
shock resistance			
 according to IEC 60068-2-27 	30g / 11 ms		
 for railway applications according to EN 61373 	Category 1, Class B		
vibration resistance			
 according to IEC 60068-2-6 	0.35 mm/5g		
 for railway applications according to EN 61373 	Category 1, Class B		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
material of the enclosure of the switch head	plastic		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	20 N		
length of the sensor	75.7 mm		
width of the sensor	31 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		

General Product Approval	Confirmation) <u>KC</u>	EAC	
General Product Approval				
Certificates/ approvals				
fastening method	screw fixing			
mounting position	any			
Installation/ mounting/ dimensions				
explosion protection category for dust	none			
during storage	-40 +90 °C			
 during operation 	-40 +85 °C			
ambient temperature				
Ambient conditions				
design of the interface	without			
Communication/ Protocol				
cable entry type	1x (M20 x 1.5)			
 at AWG cables stranded 	1x (20 16), 2x (2	20 18)		
at AWG cables solid	1x (20 16), 2x (2			
 finely stranded with core end processing 		1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
• solid		²), 2x (0.5 0.75 mm²)		
type of connectable conductor cross-section				
type of electrical connection	screw-type termina	als		
Connections/ Terminals				
number of switching contacts safety-related	1			
circuit principle	snap-action contac	cts		
design of the switching function	positive opening			
shape of the switch head	rounded	0		
standard-compliant actuator head	EN 50047, design			
design of the actuating element	Rounded plunger,	plastic plunger		
Drive Head				
design of the housing according to standar				
coating of the enclosure	Other types			
design of the housing material of the enclosure	block, narrow			
Enclosure	black generation			
design of the interface for safety-related comm	nunication without			
at 400 V rated value	0.12 A			
 at 250 V rated value 	0.27 A			
 at 125 V rated value 	0.55 A			
 at 24 V rated value 	3 A			
operational current at DC-13				
 at 400 V rated value 	4 A			
 at 240 V rated value 	6 A			
• at 120 V rated value	6 A			
 at 24 V rated value 	6 A			
operational current at AC-15				
number of NC contacts for auxiliary contact number of NO contacts for auxiliary contact				
	its 1			



<u>Type Examination</u> <u>Certificate</u>





<u>Type Test Certific-</u> <u>ates/Test Report</u> Type Test Certificates/Test Report

other

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10 Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5232-0CC05-1AJ0

Cax online generator

 $\underline{http://support.automation.siemens.com/WW/CAX order/default.aspx?lang=en\&mlfb=3SE5232-0CC05-1AJ0$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5232-0CC05-1AJ0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5232-0CC05-1AJ0&lang=en

last modified:

3/23/2022 🖸