SIEMENS

Data sheet

3SE5234-0CD03-1AJ1



Position switch Plastic 31 mm according to EN 50047 Increased corrosion protection with M12 connector plug, 4-pole 1 NO/1 NC quick action contacts Roller plunger with plastic roller 10 mm functional at -40 °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied actuator head for position switches 	3SE5000-0AD03		
 of the supplied switching contacts 	<u>3SE5000-0CA00</u>		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	250 V		
degree of pollution	class 3		
surge voltage resistance rated value	3 kV		
protection class IP	IP65		
shock resistance			
 according to IEC 60068-2-27 	30g / 11 ms		
 for railway applications according to EN 61373 	Category 1, Class B		
vibration resistance			
 according to IEC 60068-2-6 	0.35 mm/5g		
 for railway applications according to EN 61373 	Category 1, Class B		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	4 A		
material of the enclosure of the switch head	plastic		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	4 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	4 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	20 N		
length of the sensor	100 mm		
width of the sensor	31 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	1		

number of NO contacts for auxiliary contacts	1			
operational current at AC-15				
at 24 V rated value	4 A			
at 125 V rated value	4 A			
at 240 V rated value	4 A			
operational current at DC-13				
at 24 V rated value	3 A			
• at 125 V rated value	0.55 A			
• at 250 V rated value	0.33 A			
design of the interface for safety-related communication	without			
Enclosure				
design of the housing	block, narrow			
material of the enclosure	plastic			
coating of the enclosure	Other types			
design of the housing according to standard	Yes			
Drive Head				
design of the actuating element	Roller plunger, plastic roller			
standard-compliant actuator head	EN 50047, design C			
shape of the switch head	roller			
design of the switching function	positive opening			
circuit principle	snap-action contacts			
number of switching contacts safety-related	1			
Connections/ Terminals				
type of electrical connection	M12 plug, fixed			
cable entry type	M12 plug			
design of plug-in connection	M12 plug, 4-pole: Pin 1 = terminal 21, Pin 2 = 22, Pin 3 = 13, Pin 4 = 14			
Communication/ Protocol	····- p····3, · · p ····· · · · ·			
design of the interface	without			
Ambient conditions	Without			
ambient temperature				
during operation	-40 +85 °C			
during storage	-40 +85 C -40 +90 °C			
explosion protection category for dust	none			
Installation/ mounting/ dimensions	none			
	201/			
fastening method	any screw fixing			
Certificates/ approvals	Screw lixing			
General Product Approval				
		EHC	EHC	
Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates	other		
Type Examination Certificate Left <	<u>Type Test Certific-</u> ates/Test Report	<u>Confirmation</u>		

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5234-0CD03-1AJ1 Cax online generator

Subject to change without notice © Copyright Siemens http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5234-0CD03-1AJ1 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5234-0CD03-1AJ1 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5234-0CD03-1AJ1&lang=en

last modified:

3/23/2022 🖸