SIEMENS

Data sheet

3SE5112-0CA00



Basic switch for position switch 3SE51 Metal enclosure, according to EN 50041 Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts without actuator head

product brand name	SIRIUS
product designation	Mechanical safety switches
product type designation	3SE5
manufacturer's article number	56E5
of the supplied switching contacts	3SE5000-0CA00
 of the supplied switching contacts of the supplied empty enclosure with cover 	3SE5112-0AA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
 according to IEC 60068-2-27 	30g / 11 ms
vibration resistance according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	85.7 mm
width of the sensor	40 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current at AC-15	

 at 24 V rated value 	alue	6 A				
 at 125 V rated v 	value	6 A				
 at 240 V rated v 	value	6 A	6 A			
 at 400 V rated v 	value	4 A				
operational current	at DC-13					
 at 24 V rated value 	alue	3 A				
• at 125 V rated	at 125 V rated value		0.55 A			
 at 250 V rated v 	value	0.2	0.27 A			
• at 400 V rated	value	0.1	2 A			
design of the interface	e for safety-related commu	nication with	without			
Enclosure						
design of the housin		block, narrow				
material of the enclo	-		metal			
coating of the enclo						
_	ng according to standard		cathodic dip coating			
_	ig according to standard	Tes	,			
Drive Head						
	design of the actuating element Other, without, basic switch					
design of the switch	ing function		Positive opening with appropriate positive opening actuator head			
circuit principle			snap-action contacts			
number of switching contacts safety-related 1						
Connections/ Termina	als					
type of electrical co	nnection	scr	ew-type terminals			
type of connectable	conductor cross-section	IS				
 solid 		1x (1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)			
 finely stranded 	with core end processing	1x (1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)			
 at AWG cables 				1x (20 16), 2x (20 18)		
• at AWG cables stranded 1x (20 16), 2x (20 18)						
cable entry type 1x (M20 x 1.5)						
Communication/ Prot	ocol		,			
design of the interfa		varith				
Ambient conditions			without			
	-	_			_	
ambient temperature						
during operation			-25 +85 °C			
during storage			-40 +90 °C			
			none			
Installation/ mounting	/ dimensions					
mounting position		any				
fastening method			screw fixing			
Certificates/ approval	S					
General Product Ap	oproval					
	Confirmation					
(SĐ		(000)	(Ų_)	EAC	LHI	
				LIIL	LIIL	
CSA		ccc	UL			
Functional						
Safety/Safety of	Declaration of Conform	nity	Test Certificates	other		
Machinery						
_			- - - - -			
Type Examination Certificate	ŪK	((<u>Type Test Certific-</u> ates/Test Report	Confirmation		
CERTINGALE	ĊÀ	Œ	ales rest reput			
	LH	EG-Konf.				
Eurther information						

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5112-0CA00 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5112-0CA00 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5112-0CA00 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5112-0CA00&lang=en

last modified:

3/23/2022 🖸