SIEMENS

Data sheet 3SE5122-0BH50



Position switch Metal enclosure 56 mm wide Device connection $3x \, (M20x \, 1.5) \, 1 \, NO/1 \, NC$ slow-action contacts Rotary actuator right/left adjustable, with adjustable-length metal lever 100 mm long and plastic roller 19 mm

product brand name	SIRIUS	
product designation	Mechanical position switches	
product type designation	3SE5	
manufacturer's article number		
 of the supplied basic switch 	3SE5122-0BA00	
 of the supplied actuator head for position switches 	3SE5000-0AH00	
 of the supplied operating lever 	3SE5000-0AA50	
 of the supplied switching contacts 	3SE5000-0BA00	
 of the supplied empty enclosure with cover 	3SE5122-0AA00	
suitability for use safety switch	No	
General technical data		
product function positive opening	No	
insulation voltage rated value	400 V	
degree of pollution	class 3	
surge voltage resistance rated value	6 kV	
protection class IP	IP66/IP67	
shock resistance		
according to IEC 60068-2-27	30g / 11 ms	
vibration resistance according to IEC 60068-2-6	0.35 mm/5g	
mechanical service life (switching cycles) typical	15 000 000	
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000	
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000	
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000	
thermal current	10 A	
material of the enclosure of the switch head	plastic	
reference code according to IEC 81346-2	В	
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A	
continuous current of the DIAZED fuse link gG	6 A	
active principle	mechanical	
repeat accuracy	0.05 mm	
Substance Prohibitance (Date)	07/01/2006	
minimum actuating torque in directions of actuation	0.25 N·m	
length of the sensor	192 mm	
width of the sensor	56 mm	
design of the switching contact	mechanical	

operating frequency rated value	50 60 Hz	
number of NC contacts for auxiliary contacts		
	1	
number of NO contacts for auxiliary contacts operational current at AC-15		
•	0.4	
at 24 V rated value	6 A	
• at 125 V rated value	6 A	
• at 240 V rated value	6 A	
at 400 V rated value	4 A	
operational current at DC-13		
at 24 V rated value	3 A	
at 125 V rated value	0.55 A	
 at 250 V rated value 	0.27 A	
at 400 V rated value	0.12 A	
design of the interface for safety-related communication	without	
Enclosure		
design of the housing	block, wide	
material of the enclosure	metal	
coating of the enclosure	cathodic dip coating	
design of the housing according to standard	No	
Drive Head		
design of the actuating element	Adjustable twist lever, adjustable-length metal lever, plastic roller 19 mm	
standard-compliant actuator head	EN 50041, design A	
shape of the switch head	roller	
circuit principle	slow-action contacts	
number of switching contacts safety-related	0	
Connections/ Terminals		
type of electrical connection	screw-type terminals	
type of connectable conductor cross-sections		
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)	
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)	
 at AWG cables solid 	1x (20 16), 2x (20 18)	
 at AWG cables stranded 	1x (20 16), 2x (20 18)	
cable entry type	3x (M20 x 1.5)	
Communication/ Protocol		
design of the interface	without	
Ambient conditions		
ambient temperature		
during operation	-25 +85 °C	
during storage	-40 +90 °C	
explosion protection category for dust	none	
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	screw fixing	
Certificates/ approvals		
General Product Approval		



Confirmation









Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates	other
---	-------------------	-------





Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5122-0BH50

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5122-0BH50

 ${\bf Service \& Support \ (Manuals, \ Certificates, \ Characteristics, \ FAQs, ...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3SE5122-0BH50

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5122-0BH50&lang=en

last modified:	1/26/2022