SIEMENS

Data sheet

3SE5232-0LC05-1AJ0



Position switch Plastic 31 mm according to EN 50047 Increased corrosion protection Device connection 1 x (M20 x 1.5) 1 NO/2 NC quick action contacts Rounded plunger functional at -40 °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS	
product designation	Mechanical position switches	
product type designation	3SE5	
manufacturer's article number		
 of the supplied switching contacts 	<u>3SE5000-0LA00</u>	
suitability for use safety switch	Yes	
General technical data		
product function positive opening	Yes	
insulation voltage rated value	400 V	
degree of pollution	class 3	
surge voltage resistance rated value	6 kV	
protection class IP	IP65	
shock resistance		
 according to IEC 60068-2-27 	30g / 11 ms	
 for railway applications according to EN 61373 	Category 1, Class B	
vibration resistance		
 according to IEC 60068-2-6 	0.35 mm/5g	
 for railway applications according to EN 61373 	Category 1, Class B	
mechanical service life (switching cycles) typical	15 000 000	
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000	
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000	
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000	
thermal current	10 A	
material of the enclosure of the switch head	plastic	
reference code according to IEC 81346-2	В	
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A	
continuous current of the DIAZED fuse link gG	6 A	
active principle	mechanical	
repeat accuracy	0.05 mm	
Substance Prohibitance (Date)	07/01/2006	
minimum actuating force in directions of actuation	20 N	
length of the sensor	75.7 mm	
width of the sensor	31 mm	
design of the switching contact	mechanical	
operating frequency rated value	50 60 Hz	

number of NC contacts for auxiliary contacts	2	
number of NO contacts for auxiliary contacts	1	
operational current at AC-15		
 at 24 V rated value 	6 A	
 at 120 V rated value 	6 A	
 at 240 V rated value 	6 A	
at 400 V rated value	4 A	
operational current at DC-13		
 at 24 V rated value 	3 A	
 at 125 V rated value 	0.55 A	
 at 250 V rated value 	0.27 A	
at 400 V rated value	0.12 A	
design of the interface for safety-related communication	without	
Enclosure		
design of the housing	block, narrow	
material of the enclosure	plastic	
coating of the enclosure	Other types	
design of the housing according to standard	Yes	
Drive Head		
design of the actuating element	Rounded plunger, plastic plunger	
standard-compliant actuator head	EN 50047, design B	
shape of the switch head	rounded	
design of the switching function	positive opening	
circuit principle	snap-action contacts	
number of switching contacts safety-related	2	
Connections/ Terminals		
type of electrical connection	screw-type terminals	
type of connectable conductor cross-sections		
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)	
 finely stranded with core end processing 	1x (0.5 1.5 mm ²), 2x (0.5 0.75 mm ²)	
at AWG cables solid	1x (20 16), 2x (20 18)	
at AWG cables stranded	1x (20 16), 2x (20 18)	
cable entry type	1x (M20 x 1.5)	
Communication/ Protocol		
design of the interface	without	
Ambient conditions	without	
ambient temperature	40 195 °C	
during operation	-40 +85 °C	
during storage	-40 +90 °C	
explosion protection category for dust	none	
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	screw fixing	
Certificates/ approvals		
General Product Approval		
Confirmation CSA		EHC
Functional		





UK CA

Type Test Certificates/Test Report Type Test Certificates/Test Report **Confirmation**

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5232-0LC05-1AJ0


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5232-0LC05-1AJ0


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5232-0LC05-1AJ0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5232-0LC05-1AJ0&lang=en







last modified:

3/23/2022 🖸