

Data Sheet SMT-0830-T-HT-R


PUI Audio's **High-Temp** line of products is designed with ultra-wide operating temperatures. The **SMT-0830-T-HT-R** is designed for high output at 3000 Hz in a small package.

- 90dB output with 3.6 V0-p and 3000 Hz input
- Has a wide operating temperature range of -40°C \sim +105°C
- Only weighs 0.4 grams


Specifications

| Parameters | Values | Units |
|-------------------------------|----------------------------|--------------------------------------|
| Rated Voltage | 3.6 | V0-p |
| Operating Voltage Range | 2 ~ 5 | V0-p |
| Current Draw at Rated Voltage | ≤100 | mA |
| Coil Resistance | 16±3 | Ohms |
| Minimum SPL @ 10cm | ≥90 | dBA |
| Resonant Frequency | 3000±500 | Hz |
| Housing Material | LCP | - |
| Weight | 0.4 | Grams |
| Acceptable Soldering Methods | Hand Solder, Reflow Solder | See page 2 for soldering information |
| Environmental Compliances | RoHS | - |
| Storage Temperature | -40 ~ +120 | °C |
| Operating Temperature | -40 ~ +105 | °C |


$\textbf{Measurement Method}_{\text{(3.6V0-p, 3000Hz, 50\% duty cycle square wave with a SPL meter at 10cm)}}$



Typical Frequency Response (3.6 VO-p sine-sweep with microphone spaced at 10cm)



Recommended Soldering Procedure




| Profile Feature | Pb-Free Assembly |
|---|------------------|
| Average ramp-up rate(T _L to Tp) | 3℃/second max. |
| Preheat | |
| -Temperature Min.(Ts _{min}) | 150℃ |
| -Temperature Min.(Ts _{max}) | 200℃ |
| -Temperature Min.(ts) | 60∼180 seconds |
| Ts _{max} to T _L | |
| -Ramp-up Rate | 3℃/second max. |
| Time maintained above: | |
| - Temperature(T _L) | 217℃ |
| -Time(T _L) | 60∼150 seconds |
| Peak temperature(Tp) | 250℃+0/-5℃ |
| Time within 5°C of actual Peak temperature (tp) | 6 seconds max. |
| Ramp-down Rate | 6℃/second max. |
| Time 25°C to Peak Temperature | 8 minutes max. |

Reliability Testing


| Type of Test | Test Specifications |
|---------------------------|---|
| | The part shall be capable of withstanding a |
| High Temperature Test | storage temperature of +120°C for 120 hours |
| | The part shall be capable of withstanding a |
| Low Temperature Test | storage temperature of -40°C for 120 hours |
| Humidity Test | 40±2°C, 90∼95% RH, 120 hours |
| | Total 5 cycles, 1 cycle consisting of: |
| | -40±2°C, 30 minutes |
| | 20±5°C, 15 minutes |
| | 120±2°C, 30 minutes |
| Temperature Cycle Testing | 20±5°C, 15 minutes |
| | The part shall be subjected to a vibration |
| | cycle of 10Hz in a period of 1 minute. Total |
| | peak amplitude shall be 1.52mm (9.3g). |
| | The vibration test shall consist of 2 hours per |
| | plane in each three mutually perpendicular |
| Vibration Test | planes for a total time of 6 hours. |
| | Sounder shall be measured after being |
| | applied a shock (980m/s ²) for each three |
| | mutually perpendicular directions to each of |
| Shock Test | 3 times by a half sine wave. |
| | Dropped from 7m onto the surface of a |
| | 10mm thick wooden board. Applied to the |
| Drop Test | top and side of the part. |

² hours after the test the part shall meet specifications without any degradation in appearance and performance except SPL shall be within $\pm 10 dB$ of the initial value.

Dimensions (Tolerance: ±0.5mm Units: mm)




Suggested Land Pattern*




*This land pattern is advisory only and its use or adaptation is entirely voluntary. PUI Audio disclaims all liability of any kind associated with the use, application, or adaptation of this land pattern.

Packaging



Packaging Cont'd



NOTES:

- 1.1000 PCS per box
- 2.Total 10 boxes per carton
- 3.Total 10000 PCS carton

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2020, PUI Audio Inc.

Specifications Revisions

| Revision | Description | Date |
|----------|---------------------------|--------|
| - | Released from Engineering | 4/1/20 |

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- $2. \quad Specifications \ subject \ to \ change \ or \ with drawal \ without \ notice.$